



### Main

Range	Sequence5
Product or component type	Electronic room thermostat
Device presentation	Complete product
Device application	Heating Cooling
Colour tint	Nickel
Surface finish	Glossy
Type of packing	Box
Quantity per set	Set of 1
Sale per indivisible quantity	1
Number of terminals	5 screw terminals

### Complementary

Device mounting	Flush
Control type	Turn button
Fixing mode	By screws
Temperature setting range	5...30 °C
Measurement accuracy	+/- 0.5 °C
Contacts type and composition	NC NO
[In] rated current	8 A (resistive load) 5 A (inductive load) 0.6
[Ue] rated operational voltage	230 V AC 50 Hz
Protection type	Fuse protection
Associated fuse rating	10 A
Shape of screw head	Pozidriv No 1
Clamping connection capacity	2 x 1.5...1 x 2.5 mm <sup>2</sup> flexible 2 x 1.5...1 x 2.5 mm <sup>2</sup> solid 2 x 1.5...1 x 2.5 mm <sup>2</sup> stranded
Wire stripping length	8 mm
Local signalling	1 LED green presence of voltage 1 dual colour LED red/blue heating or air-conditioning application
Material	Metal

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	80 mm
Width	80 mm
Depth	54 mm
Embedding depth	44 mm
Product weight	0.221 kg

## Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	0...35 °C
Relative humidity	0...95 %
Standards	2004/108/EC EN 60730-2-9 2006/95/EEC
Product certifications	N Cenelec CCA-FI_2316
IK degree of protection	IK04
IP degree of protection	IP20