

# Product data sheet

Specifications



## Sedna - 1pole 2way switch - titanium DIY

SDN0400268

⚠ Discontinued on: Dec 30, 2023

⚠ Discontinued

### Main

Range Name	Sedna
Product Or Component Type	Switch
Delivery Form	Complete product
Cover Plate Color	Titanium
Function	1-pole 2-way switch
Type Of Packing	Blister
Rated Current	10 AX at 250 V AC

### Complementary

Installation	Flush
Height	80 mm
Material Of Visible Parts	Thermoplastic ABS-UV stabilised
Power Range	2300 W
Net Weight	0.0878 kg
Depth	37 mm
Surface Finish	Glossy
Wire Stripping Length	13 mm
Fixing Mode	Screws or claws 51...70 mm
Terminal Capacity	2 cable(s) 2.5 mm²

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.800 cm
Package 1 Width	11.000 cm
Package 1 Length	15.000 cm
Package 1 Weight	85.000 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	8
Package 2 Height	10.000 cm
Package 2 Width	20.500 cm
Package 2 Length	31.000 cm
Package 2 Weight	794.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	40
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	4.314 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations