



Main

Range	Sedna
Function	Data socket
Device application	Communication
Delivery form	Without frame
Connector shielding type	STP
Data connector type	RJ45 - 4 contacts
Cover plate color	Beige

Complementary

Communication network category	5e
Socket number	2
Wire structure	Rigid
Kind of terminals	Screw connection
Material of visible parts	Thermoplastic ABS-UV stabilised
Surface finish	Glossy
Installation direction	Straight
Installation	Flush
Fixing mode	Claws, span of claws working range : 51...80 mm Screws
Height	71 mm
Width	71 mm
Depth	36 mm
Depth of visual part	14.5 mm
Product weight	0.09568 kg

Environment

IP degree of protection	IP20
-------------------------	------

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1136 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
------------------------	---

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
Contractual warranty	
Warranty period	18 months