



Main

Range of product	Zelio Relay
Product or component type	Solid state relay
Device short name	SSM
Number of channels	1
Number of phases	1 phase

Complementary

Mounting support	Symmetrical DIN rail
[In] rated current	6 A
Output voltage	24...280 V AC
[Uc] control circuit voltage	90...140 V AC
Contacts type and configuration	1 NO
Tightening torque	Input : 0.5...0.8 N.m Output : 0.5...0.8 N.m
Connections - terminals	Screw terminals : 1 x 0.3...1 x 1.5 mm ² , (AWG 22...AWG 16) for input Screw terminals : 1 x 0.3...1 x 2.5 mm ² , (AWG 22...AWG 14) for output
Maximum capacitance	10 pF for input/output
Insulation resistance	1000 MOhm at 500 V DC
Local signalling	LED green for input status
Minimum switching voltage	90 V AC turn-on
Maximum switching voltage	10 V AC turn-off
Input current	3...5 mA
Solid state output type	Zero voltage switching SCR output
Load current	0.15...6 A
Transient overvoltage	600 V
Surge current	285 A for 16.6 ms 300 A for 20 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Voltage drop	<= 1.3 V on-state
Motor power hp	0.16 hp at <= 40 °C 240 V AC
Maximum I ² t for fusing	375 A ² .s for 8.33 ms at 60 Hz half cycle 410 A ² .s for 10 ms at 50 Hz half cycle
Leakage current	<= 0.1 mA off-state
DV/Dt	500 V/μs off-state at maximum voltage
Response time	30 ms turn-off 0.5 cycle turn-on
Power factor	0.5 with maximum load
Overvoltage category	III
Width	11 mm
Height	90.3 mm
Depth	83.7 mm
Product weight	0.05 kg


Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	4 kV AC for input/output 4 kV AC for input or output to case
Pollution degree	2
Standards	IEC 61000 IEC 60950-1 IEC 62314
Product certifications	CSA UL REACH
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-30...80 °C
Ambient air temperature for storage	-30...100 °C


Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1328 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Dimensions



Derating Curves



- A : Load Current (Amperes)
- B : Ambient Temperature (°C)
- 1 : Multiple units, no minimum spacing between components
- 2 : Installed single unit, distance to adjacent components more than 11 mm