

### Main

Range of product	Modicon M171/M172
Product or component type	Additional I/O module
Product specific application	HVAC and pumping solution
Total inputs/outputs	27
Discrete input number	8
Discrete output number	3For relay outputs SPST with same common 2For relay outputs SPST with same common 2For relay outputs SPDT with independent common
Discrete output current	8 AFor relay SPDT 5 AFor relay SPST
Analogue input number	2 analog input NTC 4 configurable
Analogue output number	3 voltage/current 4...20 mA or 0...10 V 2 open collector 1 kHz, 12 V, 35 mA

### Complementary

Number of port	1 CAN port - screw terminal block
Input/Output number	6 analog input(s) 5 analog output(s) 8 digital input(s) 7 digital output(s) 1 high-speed counter(s)
Discrete input logic	Sink or source (positive/negative)
Discrete input voltage	24 V AC/DC 48 V DC
Discrete input current	2.5 mA
Input impedance	20 kOhm
Analogue input type	Direct input Impedance 0...1500 hOhm Impedance 0...300 daOhm Voltage 0...5 V (ratiometric) Pt 1000 temperature probe - 200...800 °C - resolution: 0.1 °C NTC temperature probe - 50...110 °C - resolution: 0.1 °C (extended)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

NTC temperature probe - 40...150 °C - resolution: 0.1 °C  
 Current 4...20 mA  
 Voltage 0...10 V

Sensor power supply	5 V DC at 50 mA 12 V DC at 150 mA
[Us] rated supply voltage	48 V 24 V AC
Realtime clock	Without clock at -20...55 °C
Display type	Without display
Overvoltage category	II
Mounting support	DIN rail
Width	140 mm
Height	110 mm
Depth	61.6 mm
Product weight	0.19 kg


## Environment

Directives	2006/95/EC - low voltage directive 86/188/EEC - physical agents (noise) directive 2011/65/EU - RoHS directive 1907/2006/EC - REACH directive
Standards	EN/IEC 60730
Product certifications	CE CSA cURus EAC
Ambient air temperature for operation	-20...55 °C conforming to UL 60730-1
Ambient air temperature for storage	-40...85 °C
Relative humidity	10...90 % non-condensing
IP degree of protection	IP20
Pollution degree	2

## Offer Sustainability


Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1427 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

Dimensions




Mounting and Clearance


Clearance




Misplacement




Power Supply



Digital Inputs




Analog Inputs




(1) Max current: 50 mA.  
G : Ground

Analog Outputs






Digital Outputs



C : common


Fast Digital Input



---


Serial Line Port (RS 485)

---



Apply 120 Ohm terminal resistance  
GS serial GND isolated from G

CAN Expansion Bus




- (1) CAN terminal resistance
- (2) Output for remote keyboard
- (3) CANOPEN
- (4) Power Out

---


4 DipSwitches

---



(1) 4 DIP SWITCH  
LOW Address

6 - 10 DipSwitches



- (1) 10 DIP SWITCH
- (2) 6 DIP SWITCH