



Main

Range of product	Modicon Premium Automation platform
Product or component type	Unity processor
Software designation	Unity Pro

Complementary

Number of racks	2 12 slots 4 4/6/8 slots
Number of slots	16 24 32
Discrete I/O processor capacity	512 I/O
Analogue I/O processor capacity	24 I/O
Number of application specific channel	<= 8
Integrated connection type	Fipio manager (63 agents) SUB-D 9 Non isolated serial link 2 female mini DIN RS485 19.2 kbit/s
Communication module processor capacity	1 2
Memory description	Internal RAM (with PCMCIA card) 224 kB program Internal RAM (with PCMCIA card) 96 kB data Internal RAM (without PCMCIA card) 96 kB program and data PCMCIA card 256 kB additional data storage
Maximum size of object areas	32 kB (elementary and derived data) unlocated internal data 4096 %Mi located internal bits 64 %KWi constant words located internal data 64 %MWi internal words located internal data 64 kB (DFB and EFB function blocks) unlocated internal data
Application structure	1 fast task 1 master task 32 event tasks
Execution time per instruction	0.19 µs Boolean without PCMCIA card 0.25 µs Boolean with PCMCIA card 0.25 µs word or fixed-point arithmetic without PCMCIA card 0.5 µs word or fixed-point arithmetic with PCMCIA card 1.75...2.6 µs floating points with PCMCIA card 1.75...2.6 µs floating points without PCMCIA card
Number of instructions per ms	2.1 Kinst/ms 65 % Boolean + 35 % fixed arithmetic with PCMCIA card 3.1 Kinst/ms 100 % Boolean with PCMCIA card 3.71 Kinst/ms 65 % Boolean + 35 % fixed arithmetic without PCMCIA card

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

	4.76 Kinst/ms 100 % Boolean without PCMCIA card
System overhead	0.3 ms fast task 1 ms master task
Marking	CE
Local signalling	1 LED green processor running (RUN) 1 LED red activity on Fipio bus (FIP) 1 LED red I/O module or configuration fault (I/O) 1 LED red processor or system fault (ERR) 1 LED yellow activity on TER or AUX terminal port (TER)
Current consumption	930 mA 5 V DC
Module format	Standard
Product weight	0.42 kg

Environment

Standards	73/23/EEC 89/336/EEC 92/31/EEC 93/68/EEC CSA C22.2 No 142 IEC 61131-2 UL 508 CSA C22.2 No 213 Class I Division 2 Group A CSA C22.2 No 213 Class I Division 2 Group B CSA C22.2 No 213 Class I Division 2 Group C CSA C22.2 No 213 Class I Division 2 Group D
Product certifications	ABS BV DNV GL LR RINA RMRS
Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-25...70 °C
Relative humidity	10...95 % without condensation for operation 5...95 % without condensation for storage
Operating altitude	0...2000 m
Protective treatment	TC
IP degree of protection	IP20
Pollution degree	2

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0932 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

TSXP57154M is replaced by:



Standard environment BMEP581020

processor module M580 - Level 1 - Distributed

Qty 1

Reason for Substitution: End of life | Substitution date: 31 December 2018 | Not same dimensions/design - better performances, more services provided
