



Main

Range of product	SM6
Technology type	Air insulated switchgear
Device short name	QM 375
Product or component type	Fuse-switch
Internal arc protection	12.5 kA 1 s
Network type	AC
VPIS	9...17.9 kV
Cable connection	1 x 95 mm ² per phase

Complementary

Bus rated current	630 A
Type of operator	C11 manual
Protection type	Fuse
Product weight	120 kg

Environment

Width	375 mm
Depth	940 mm
Standards	IEC 62271-100
Ambient air temperature for operation	-5...40 °C
Colour code	RAL 9003
Ambient air temperature for storage	-40...70 °C
IP degree of protection	IP3x
Vibration resistance	0.5 gn horizontal class 2 0.4 gn vertical class 2
Operating altitude	<= 1000 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications