



### Main

Range of product	Hyde Park
Sensor type	Ultrasonic sensor
Series name	Superprox 900
Device short name	SM906
Sensor design	Cylindrical M30
[Sn] nominal sensing distance	2 m
Type of sensing window	Adjustable
Material	Plastic
Enclosure material	ULTEM
Front material	Silicone rubber
Type of output signal	Analog
ISO thread	M30 x 1.5
Wiring technique	4-wire
[Us] rated supply voltage	15...24 V DC (overload and short-circuit protection)
Supply voltage limits	13...28 V DC
Analogue output range	4...20 mA direct
Electrical connection	Cable 3 m
Product specific application	-

### Complementary

[Sd] sensing range	0.12...2 m
[Sa] assured operating distance	0.12...2 m with teach push-button
Maximum differential travel	2.5 mm
Blind zone	0...120 mm
Transmission frequency	200 kHz
Repeat accuracy	0.9 %
Beam angle	10 °
Minimum size of detected object	Cylinder diameter 1.6 mm - up to 305 mm sensing distance
Current consumption	80 mA
Maximum switching current	60 mA (reverse polarity protection)
Resistance to electrostatic discharge	8 kV (level 4) conforming to IEC 61000-4-2

Height	30 mm
Width	34.7 mm
Depth	30 mm
Length	95 mm
Product weight	0.27 kg

## Environment

Product certifications	UL
Marking	CE
NEMA degree of protection	NEMA 4X (indoor use only)
IP degree of protection	IP67
Ambient air temperature for operation	0...50 °C
Ambient air temperature for storage	-20...80 °C
Relative humidity	100 % without condensation
Vibration resistance	+/-1 mm conforming to IEC 60068-2-6 10...55 Hz
Shock resistance	30 gn in all 3 axes for 11 ms conforming to IEC 60068-2-27
Resistance to electromagnetic fields	10 V/m (level 3) conforming to IEC 61000-4-3
Resistance to fast transients	1 kV (level 3) conforming to IEC 61000-4-4

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product end of life instructions	Available <a href="#">End of Life Information</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------