



### Overview

Model Name	Schneider online UPS 1000VA
Includes	CD with software , User Manual
Product Distribution	China

### Output

Output Power Capacity	800 Watts / 1000 VA
Max Configurable Power (Watts)	800 Watts / 1000 VA
Nominal Output Voltage	220V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 2%
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Other Output Voltages	230V
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(3) Chinese outlet (Battery Backup)
Output Voltage Tolerance	+/- 2% static and 100% load step
Output Voltage THD	< 3% linear load
Bypass	Built-in Bypass

### Input

Nominal Input Voltage	220V
Input Frequency	47 - 70 Hz (auto sensing)
Input Connections	IEC-320 C14
Cord Length	1.83 meters
Input voltage range for main operations	140 - 300 V
Other Input Voltages	230 , 240
Maximum Input Current	7 A
Input Breaker Capacity	10 A
Input Total Harmonic Distortion	Less than 10% for the full load

## Batteries & Runtime

Battery Type	VRLA
Typical recharge time	4 hour(s)
RBC Quantity	3
Efficiency in Battery Operation	83.00 %

## Communications & Management

Interface Port(s)	DB-9 RS-232 , SmartSlot
Available SmartSlot™ Interface Quantity	1
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rating	600 Joules
---------------------	------------

## Physical

Maximum Height	220.0 mm
Maximum Width	145.0 mm
Maximum Depth	397.0 mm
Net Weight	13.0 kg
Shipping Weight	14.0 kg
Shipping Height	325.0 mm
Shipping Width	230.0 mm
Shipping Depth	472.0 mm
SCC Codes	1073130431111 6

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 90 %
Operating Elevation	0-999.9 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 90 %
Storage Elevation	0-999.9 meters
Audible noise at 1 meter from surface of unit	50.000 dB
Protection Class	IP 20

## Conformance

Approvals	CE , CE Mark , EN/IEC 62040-3 , IEC 62040-1-1
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
Other Environmental Compliance	China RoHS