

Product data sheet

Specifications

Actassi - equipped optic cassette LC/MTP - 0.5U - OM3



VDILC135C1C

⚠ Discontinued on: Sep 30, 2022

⚠ Discontinued

Main

Product Or Component Type	Equipped optic cassette
Colour	Cassette: black (RAL 9005) LC adapter: aqua MTP adapter: aqua
Type Of Paint	Cassette: epoxy
Quantity Per Set	1

Complementary

Product Destination	Empty fibre optic panel Overhead support
Termination 1	6 x LC duplex
Termination 2	1 x 12 MTP
Minimum Return Loss	20 dB 850 nm MTP 20 dB 850 nm LC
Maximum Insertion Loss	MTP: <0.5 dB at 850 nm LC: <0.3 dB at 850 nm
Number Of Rack Unit	0.5U
Fibre Performance	OM3
Material	Aluminium alloy: cassette PBT (polybutylene terephthalate): LC adapter PEI (polyetherimide): MTP adapter
Type Of Installation	Indoor
Device Mounting	Flush
Mounting Type	By captive screws
Height	18 mm
Width	105 mm
Depth	124.5 mm
Targeted Region	Europe

Environment

Ambient Air Temperature For Storage	-25...70 °C
Ambient Air Temperature For Operation	-10...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	LC adapter: IEC 61754-20 LC adapter: IEC 50377-7-x MTP adapter: IEC 61754-7 MTP adapter: EN 50377-15-1 MTP adapter: TIA/EIA-604-5 Performance: ISO/IEC 11801 Ed.2.2 Cabling: ISO/IEC 24764 Fibre cabling test: ISO/IEC 14763-3 TIA/EIA-568-C.3 ANSI/TIA-942 10Gbase-SR: IEEE 802.3ae
-----------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	19.0 cm
Package 1 Length	14.0 cm
Package 1 Weight	1.7 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations