


SU3000R3IX160

APC Smart-UPS 3000VA RM 3U 230V w/CISPR Class B



SU3000R3IX160 has not been replaced. Please contact your customer care center for more information.

Overview

Model Name	APC Smart-UPS 3000VA RM 3U 230V w/CISPR Class B
Includes	Rack Mounting brackets , Rack Mounting support rails , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Algeria , Angola , Armenia , Azerbaijan , Bahrain , Belarus , Benin , Bosnia And Herzegovina , Botswana , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Central African Republic , Chad , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cote D'Ivoire , Croatia , Djibouti , Egypt , Equatorial Guinea , Eritrea , Ethiopia , Gabon , Gambia , Georgia , Ghana , Gibraltar , Guinea , Iran (Islamic Republic Of) , Iraq , Israel , Jordan , Kazakhstan , Kenya , Kuwait , Lebanon , Lesotho , Liberia , Malawi , Mali , Mauritania , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Namibia , Niger , Nigeria , Oman , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Somalia , South Africa , Sudan , Suriname , Tajikistan , TANZANIA , UNITED REPUBLIC OF , Togo , Turkey , Turkmenistan , Uganda , Ukraine , United Arab Emirates , Uzbekistan , Western Sahara , Yemen , Zambia , Zimbabwe

Output

Output Power Capacity	2250 Watts / 3000 VA
Max Configurable Power (Watts)	2250 Watts / 3000 VA
Nominal Output Voltage	230V
Output Voltage Distortion	Less than 5% at full load
Output Frequency (sync to mains)	47 - 53 Hz for 50 Hz nominal , 57 - 63 Hz for 60 Hz nominal
Crest Factor	up to 5 : 1
Crest Factor	Line Interactive
Waveform Type	Sine wave
Output Connections	(8) IEC 320 C13 (Battery Backup)

Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320 C20
Input voltage range for main operations	174 - 286 V
Input voltage adjustable range for mains operation	168 - 302V

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	3 hour(s)
Replacement Battery	RBC12
RBC Quantity	1

Communications & Management

Interface Port(s)	DB-9 RS-232
Available SmartSlot™ Interface Quantity	1
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

Surge Protection and Filtering

Surge energy rating	480 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	132.0 mm
Maximum Width	483.0 mm
Maximum Depth	635.0 mm
Rack Height	3 U
Net Weight	51.36 kg
Shipping Weight	60.45 kg
Shipping Height	254.0 mm
Shipping Width	622.0 mm
Shipping Depth	953.0 mm
Color	Beige

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	47.000 dB
Online Thermal Dissipation	375.000 BTU/hr
Protection Class	--

Conformance

Approvals	C-tick , EN 50091-1 , EN 50091-2 , GOST , VDE
Standard warranty	2 years repair or replace