



### Overview

Model Name	APC Smart-UPS RT 10000VA 230V Harsh Environment
Includes	CD with software , Service Manual , Smart UPS signalling RS-232 cable , User Manual , Web/SNMP Management Card
Standard Lead Time	Usually in Stock
Product Distribution	India

### Output

Output Power Capacity	8000 Watts / 10.0 kVA
Max Configurable Power (Watts)	8000 Watts / 10.0 kVA
Nominal Output Voltage	230V
Output Voltage Note	Configurable for 220 : 230 or 240 nominal output voltage
Output Voltage Distortion	Less than 3%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz user adjustable +/- 0.1
Other Output Voltages	220, 240V
Crest Factor	3 : 1
Crest Factor	Double Conversion Online
Waveform Type	Sine wave
Output Connections	(1) Hard Wire 3-wire (H N + G) (Battery Backup) , (4) IEC 320 C13 (Battery Backup) , (4) IEC 320 C19 (Battery Backup) , (6) IEC Jumpers (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

### Input

Nominal Input Voltage	230V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	Hard Wire 3 wire (1PH+N+G) , Hard Wire 5-wire (3PH + N + G)
Input voltage range for main operations	160 - 280 V
Other Input Voltages	220 , 240
Input Total Harmonic Distortion	Less than 7% for full load

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	4
Typical recharge time	2.2 hour(s)
Replacement Battery	RBC44
RBC Quantity	2

## Communications & Management

Interface Port(s)	DB-9 RS-232 , RJ-45 10/100 Base-T , Smart-Slot
Pre-Installed SmartSlot™ Cards	AP9631
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	1265J Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Physical

Maximum Height	432.0 mm
Maximum Width	263.0 mm
Maximum Depth	736.0 mm
Rack Height	6 U
Net Weight	110.91 kg
Shipping Weight	129.09 kg
Shipping Height	552.0 mm
Shipping Width	597.0 mm
Shipping Depth	991.0 mm
Color	Black
Units per Pallet	2.0

## Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-15000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	2262.000 BTU/hr
Protection Class	IP 20

## Conformance

Approvals	C-tick , CE , EN 50091-1 , EN 50091-2 , EN 55022 Class A , EN 60950 , EN 61000-3-2 , GOST , VDE
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant