

Product data sheet

Specifications



Actassi CL-MNC6A Patchcord S/FTP 4P Cat6A 550MHz LSZH 1m Grey

VDIP185X46010

 **Discontinued on:** Dec 15, 2021

 **Discontinued**

Main

| | |
|----------------------|---|
| Range | Actassi |
| Product | Patch cord |
| Colour | Patchcord: grey |
| Quantity Per Set | 1 |
| Cable Shielding Type | S/FTP |
| Provided Component | Grey coloured clips Green coloured clips Red coloured clips |

Complementary

| | |
|---|--|
| Product Compatibility | Coloured clips red Coloured clips green Coloured clips yellow Coloured clips blue |
| Length (Customizable Value In Configurator) | 0...1 m |
| Communication Network Type | 10GBASE-T |
| Connector Type | RJ45 |
| Communication Network Category | 6 _A |
| Transmission Frequency | 550 MHz |
| Awg Gauge | AWG 26 |
| Input Impedance | 100 Ohm |
| Material | Solid bare copper: conductor PE (polyethylene): wire insulation |
| Targeted Region | Asia Pacific. Europe |

Environment

| | |
|--|-------------|
| Ambient Air Temperature For Installation | 0...50 °C |
| Ambient Air Temperature For Operation | -20...60 °C |
| Ambient Air Temperature For Storage | -20...60 °C |
| Temperature Resistance | 60 °C |
| Flame Retardance | LSZH |
| Product Certifications | Delta |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-----------|--|
| Standards | IEC 61935-2 ISO/IEC 11801:2011 Ed.2.2 EIA/TIA-568-C.2 EN 50173 Ed.3 |
|-----------|--|

Packing Units

| | |
|------------------------------|-------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2 cm |
| Package 1 Width | 16 cm |
| Package 1 Length | 20 cm |
| Package 1 Weight | 56 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|---|
|  Reach Free Of Svhc | |
|  Toxic Heavy Metal Free | |
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile | No need of specific recycling operations |