


Product data sheet

Specifications



LexCom Home Premium - APOLLO distribution centre 14" - 16 ports, white

VDIR611002

 **Discontinued on:** Nov 21, 2018

 **Discontinued**

Main

Range	LexCom Home
Product Name	LexCom Home Premium
Product Type	Distribution centre 14" with TV tap
Commercial Name	APOLLO

Complementary

Bandwidth	5...1000 MHz
Number Of Port	16
Maximum Insertion Loss	2 dB
Minimum Return Loss	18 dB
Shield Attenuation	90 dB
Material	Painted aluzink: body
Cable Entry	2 pieces 1.5" knock-outs at rear 2 pieces 2" knock-outs at bottom 2 pieces 2" knock-outs at side 2 pieces 2" knock-outs at top 3 pieces 2" knock-outs at rear
Average Impedance	75 Ohm
Type Of Keylock	Euro lock
Colour Tint	White (RAL 9010), textured epoxy polyester
Cable Length	0.5 m
Height	355.6 mm
Width	355.6 mm
Depth	100 mm
Weight	3 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	36.5 cm
Package 1 Length	36.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	5.7 kg
------------------	--------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Certifications & Standards

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)