

# Product data sheet

Specifications



## Unity processor, Modicon Premium, Internal RAM 2048kB data, Unity Pro

TSXP576634M

⚠ Discontinued - Service only

⚠ Discontinued on: Dec 31, 2018

⚠ To be end-of-service on: Dec 31, 2026

### Main

Range Of Product	Modicon Premium Automation platform
Product Or Component Type	Unity processor
Software Designation	Unity Pro

### Complementary

Concept	Transparent Ready
Number Of Racks	16 4/6/8 slots 8 12 slots
Number Of Slots	128 96 64
Discrete I/O Processor Capacity	2040 I/O
Analogue I/O Processor Capacity	512 I/O
Number Of Application Specific Channel	64
Number Of Process Control Channel	30 up to 90 simple loops
Integrated Connection Type	Non isolated serial link female mini DIN connector (RS485) (19.2 kbit/s) Ethernet TCP/IP RJ45 connector USB port (12 Mbit/s)
Port Ethernet	10BASE-T/100BASE-TX
Communication Module Processor Capacity	1 3 8 5
Memory Description	Internal RAM (with PCMCIA card) 2048 kB data Internal RAM (with PCMCIA card) 7168 kB program Internal RAM (without PCMCIA card) 2048 kB program and data PCMCIA card 16384 kB additional data storage
Maximum Size Of Object Areas	128 %MWi internal words located internal data 32768 %Mi located internal bits 64 %KW constant words located internal data Unlimited (DFB and EFB function blocks) unlocated internal data Unlimited (elementary and derived data) unlocated internal data
Application Structure	1 fast task 32 timers 1 master task 4 auxiliary tasks 128 event tasks

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Execution Time Per Instruction	0.0375...0.045 µs Boolean with PCMCIA card 0.0375...0.045 µs Boolean without PCMCIA card 0.045...0.06 µs word or fixed-point arithmetic with PCMCIA card 0.045...0.06 µs word or fixed-point arithmetic without PCMCIA card 0.48...0.56 µs floating points with PCMCIA card 0.48...0.56 µs floating points without PCMCIA card
Number Of Instructions Per Ms	14 Kinst/ms 65 % Boolean + 35 % fixed arithmetic with PCMCIA card 14 Kinst/ms 65 % Boolean + 35 % fixed arithmetic without PCMCIA card 20.26 Kinst/ms 100 % Boolean with PCMCIA card 20.26 Kinst/ms 100 % Boolean without PCMCIA card
System Overhead	0.07 ms for fast task 1 ms for master task
Marking	CE
Local Signalling	1 LED (green) for Ethernet TCP/IP port ready (RUN) 1 LED (green) for processor running (RUN) 1 LED (red) for collision detection (COL) 1 LED (red) for Ethernet TCP/IP port fault (ERR) 1 LED (red) for I/O module or configuration fault (I/O) 1 LED (red) for processor or system fault (ERR) 1 LED (yellow) for activity on TER or AUX terminal port (TER) 1 LED (yellow) for Ethernet link diagnostics (STS) 1 LED (yellow) for reception activity (RX) 1 LED (yellow) for transmission activity (TX)
Current Consumption	1880 mA at 5 V DC
Module Format	Double
Net Weight	0.61 kg

## Environment

Standards	CSA C22.2 No 213 Class I Division 2 Group C IEC 61131-2 UL 508 CSA C22.2 No 213 Class I Division 2 Group D CSA C22.2 No 213 Class I Division 2 Group B 73/23/EEC 93/68/EEC CSA C22.2 No 142 CSA C22.2 No 213 Class I Division 2 Group A 89/336/EEC 92/31/EEC
Product Certifications	DNV RINA LR GL BV RMRS ABS
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Relative Humidity	10...95 % without condensation for operation 5...95 % without condensation for storage
Operating Altitude	0...2000 m
Protective Treatment	TC
Ip Degree Of Protection	IP20
Pollution Degree	2

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	9.5 cm
Package 1 Width	18.0 cm
Package 1 Length	26.0 cm
Package 1 Weight	1.061 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.366 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

### California Proposition 65


WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

---

Dimensions Drawings

Standard and Extendable Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) With screw terminal block modules.  
(2) Maximum depth for all types of modules and their associated connectors.