

Product data sheet

Specifications



empty pendant control station XAC-F - custom openings

XACF3251

 **Discontinued on:** Mar 31, 2020

 **Discontinued**

Main

Range Of Product	Harmony XAC
Product Or Component Type	Pendant control station
Device Short Name	XACF

Complementary


Control Station Type	Double insulated
Enclosure Material	Glass reinforced polyester
Electrical Circuit Type	Control circuit
Enclosure Type	Empty enclosure
Number Of Cut-Out	30 maximum in positions requested on the order form
Control Station Colour	Yellow
Cable Entry	Rubber sleeve with stepped entry 22...35 mm
Guard Rail	With
Standards	CSA C22.2 No 14 EN/IEC 60947-5-1 UL 508
Protective Treatment	TH
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Overvoltage Category	Class II conforming to IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102
Mechanical Durability	1000000 cycles
Net Weight	2.5 kg

Contractual warranty

Warranty	18 months
----------	-----------


Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Dimensions




(1) Position Emergency STOP

Protective Cable Sleeves



(2) Internal Ø (mm/in.)


Protective Cable Sleeves



(2) Internal ø (mm/in.)

Mounting and Clearance

Mounting of Pendant Box




- 1 : Sustentation cables
- 2 : Cables clamp
- 3 : Ring

Connections and Schema


Control of Single-Speed Reversing Motor

With XESD1181 contact block, to be ordered separately



Control of 2-Speed Reversing Motor

With XESD1281 contact block, to be ordered separately



KM High speed contactor