



Main

Range	TeSys
Product name	TeSys VARIO
Device short name	VCD
Product or component type	Emergency stop switch disconnecter
Performance level	High performance
Poles description	3P
Contacts type and composition	3 NO
Network type	AC DC
Control type	Rotary handle
Rotary handle mounting style	Direct
Handle colour	Red
Handle front plate colour	Yellow
Suitability for isolation	Yes

Complementary

Rotary handle padlocking	1 to 3 padlocks 4...8 mm
Marking	0 - 1
Mounting support	Handle: door Switch: door
Fixing mode	Hole with 22.5 mm for handle
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	40 A
[Ithe] conventional enclosed thermal current	32 A
[Ie] rated operational current	29 A AC-23 Ue: 400 V
Rated operational power in W	11 kW at 690 V (AC-3)

	15 kW at 690 V (AC-23A) 11 kW at 400...415 V (AC-3) 15 kW at 500 V (AC-3) 18.5 kW at 500 V (AC-23A) 5.5 kW at 230...240 V (AC-3) 7.5 kW at 230...240 V (AC-23A) 15 kW at 400...415 V (AC-23A)
Intermittent duty class	30
Making capacity (I Rms)	400 A at 400 V AC-21A 400 A at 400 V AC-22A 400 A at 400 V AC-23A
[Icm] rated short-circuit making capacity	1 kA at 400 V at Ipeak
[Icw] rated short-time withstand Rms current	480 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 kA at 400 V - associated fuse 50 A aM 10 kA at 400 V - associated fuse 50 A gG
Breaking capacity	320 A at 400 V (AC-21A) 320 A at 400 V (AC-22A) 320 A at 400 V (AC-23A)
Device composition	Handle Switch
Mechanical durability	100000 cycles
Electrical durability	100000 cycles AC-21 30000 cycles DC-1...5
Connections - terminals	Power circuit: screw clamp terminals 10 mm ² - solid Power circuit: screw clamp terminals 6 mm ² - flexible - with cable end
Tightening torque	Power circuit: 2.1 N.m - on screw clamp terminals
Handle front plate dimension	60 x 60 mm
Height	74 mm
Width	60 mm
Net weight	0.215 kg

Environment

Standards	IEC 60947-3
Product certifications	UL GL CCC CSA
Protective treatment	TC
IP degree of protection	IP20 conforming to IEC 60529 IP65
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C
Fire resistance	960 °C conforming to IEC 60695-2-1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------
