


Product data sheet

Specifications



Copper LAN cable, Actassi, U/UTP, 4P, Cat5e, Euroclass D, 155MHz, LSZH, 305m

VDICD115118

Main

Range	Actassi
Product Or Component Type	Copper cable
Cable Packaging	Box of 305 m
Colour Tint	Green
Cable Shielding Type	U/UTP

Complementary

Type Of Cable	4 pair cables
Communication Network Category	5e
Remote Powering	PoE 15W (Power over Ethernet) PoE+ 30W (Power over Ethernet Plus)
Communication Network Type	1000BASE-T
Minimum Return Loss	Guaranteed: 20.1 dB at 100 MHz
Attenuation	Guaranteed: 22 dB @ 100 MHz
Power Sum Near-End Crosstalk [Psnext]	Guaranteed: 32.3 dB at 100 MHz
Attenuation To Crosstalk Ratio Far-End [Acrf]	Guaranteed: 24 dB at 100 MHz
Power Sum Attenuation Crosstalk Ratio Far-End [Psacrf]	21 dB at 100 MHz
Near End Crosstalk [Next]	Guaranteed: 35.3 dB at 100 MHz
Input Impedance	100 Ohm
Transverse Conversion Loss	>= 40 - 10 x log(f) dB from 1...100 MHz conforming to IEC 61156-5, ed. 2.1
Maximum Loop Resistance	183.8 Ohm per 1000 m
Segregation Class	Class b conforming to EN 50174-2
Maximum Resistance Unbalance	2 %
Pulling Force	110 N
Bending Radius	Minimum bending radius during installation: 8 x overall diameter Minimum bending radius after installation: 4 x overall diameter
Material	Solid bare copper: conductor PE (polyethylene): wire insulation PE (polyethylene): sheath
Euroclass Level	Dca s2 d1 a1
Nominal Velocity Propagation	68 %
Linear Conductor Resistance	91.9 mΩ/m
Awg Gauge	AWG 24

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Calorific Value	391 MJ/km
Cable Outer Diameter	4.9 mm
Cable Weight	30.9 kg / 1 km

Environment

Ambient Air Temperature For Installation	0...50 °C
Ambient Air Temperature For Storage	-20...60 °C
Ambient Air Temperature For Operation	-20...60 °C
Directives	2006/95/EC - low voltage directive 305/2011/EU - construction product regulation
Flame Retardance	LSZH
Standards	ISO/IEC 11801-ed. 3 performance EN 50173-1 performance EN 50174-1 performance ANSI/TIA/EIA-568-C.2 performance IEC 61156-5-ed. 2.1 performance EN 50288-3-1 performance ISO/IEC 14763-2 installation standards EN 50174-2 installation standards IEC 60332-1 flame propagation characteristics IEC 60754-1 IEC 60754-2 acidity of combustion gases IEC 61034 smoke generation

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.000 cm
Package 1 Width	36.000 cm
Package 1 Length	36.000 cm
Package 1 Weight	9.730 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	30
Package 2 Height	135.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	292.000 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations