


Product data sheet

Specifications



Actassi FL-C Fibre Cable OM4 50/125µm Loose Tube 6 fibres 2100m Euroclass D

VDICD52406L

Main

Range	Actassi
Product	Fibre optic cable multi mode
Device Application	Communication
Cable Packaging	Drum of 2100 m

Complementary

Maximum Attenuation	0.6 dB at 1300 nm 2.4 dB at 850 nm
Bandwidth	LED: 500 MHz.km at 1300 nm LED: 3500 MHz.km at 850 nm
Fibre Performance	OM4 50/125 µm
Optic Fibre Type	Loose tube diameter: 250 µm
Type Of Cable	Non armoured
Number Of Optic Fibre	6
Bending Radius	10 x overall diameter long term 20 x overall diameter short term
Pulling Force	1500 N
Crush Resistance	20000 N/m
Refractive Index Group	1.482 at 850 nm 1.477 at 1300 nm
Colour	External sheath: green, RAL 6016
Type Of Installation	Indoor/outdoor
Cabling Installation System	Cable duct
Calorific Value	0.542 MJ
Diameter	7.5 mm
Cable Weight	55 kg / 1000 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Installation	-15...40 °C
Ambient Air Temperature For Storage	-40...60 °C
Euroclass Level	Dca s2 d2 a2

Flame Retardance	LSZH
Environmental Characteristic	Rodent retardant: glass yarn Water resistant (longitudinally): gel Water resistant (longitudinally): swellable yarn UV resistant:
Standard	Cable specification conforming to IEC 60794-2 Cable test procedure conforming to IEC 60794-1-2 Fibre colour coding conforming to TIA/EIA-598-A Fibre performance conforming to IEC 60793-2-10 Type A1a.3 Fibre performance conforming to TIA-492AAAD OM4 Flame retardance conforming to IEC 60332-1 conforming to IEC 60754-2 Fibre performance conforming to ITU G.651.1 conforming to ISO/IEC 11801 Fibre performance conforming to EN 50173-1 conforming to EN 50399

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	49.0 cm
Package 1 Width	75.0 cm
Package 1 Length	75.0 cm
Package 1 Weight	10.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations