

Product data sheet

Specifications



Actassi - fanout link - SC/MTP - OM4 - 900 µm - Euroclass C

VDILL045K3K1

⚠ Discontinued on: Feb 10, 2021

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Fanout link
Colour	Sheath: magenta SC connector: magenta MTP connector: magenta
Type Of Packing	50...320 m cable drum

Complementary

Product Destination	empty fibre optic patch panel
Optic Fibre Type	Loose tube
Maximum Insertion Loss	0.5 dB 850 nm MTP 0.3 dB 850 nm SC
Minimum Return Loss	20 dB 850 nm MTP 20 dB 850 nm SC
Fibre Performance	OM4
Optic Fiber Diameter	900 µm
Sheath Type	Metallic cylinder
Condition Of Use	Indoor
Cable Outer Diameter	3.8 mm
Material	Plastic: SC connector
Cable Length	1...500 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Euroclass Level	C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	Fibre performance: ITU G.651 Cable specification: IEC 60794-2 Cable test procedure: IEC 60794-1-2 Flame retardance: IEC 60332-1 IEC 60754-1 Acidity of combustion gases: IEC 60754-2 Smoke generation: IEC 61034 Performance: ISO/IEC 11801:2011 Ed.2.2 Cabling: ISO/IEC 24764 Fibre cabling test: ISO/IEC 14763-3 TIA/EIA-568-C.3 ANSI/TIA-942 10Gbase-SR: IEEE 802.3ae SC connector: IEC 61754-4 SC connector: IEC 60874-19 MTP connector: IEC 61754-7 MTP connector: TIA/EIA-604-5 Fibre performance: IEC 60793-2-10 Type A1a.3
-----------	--