

Product data sheet

Specifications

Actassi - fanout link - LC/MTP - OS2 - 2 mm - Euroclass C



VDILL065D1K2

⚠ Discontinued on: Feb 10, 2021

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Fanout link
Colour	LC connector: blue Sheath: yellow MTP connector: green
Type Of Packing	50...320 m cable drum

Complementary

Product Destination	empty fibre optic patch panel
Optic Fibre Type	Loose tube
Maximum Insertion Loss	0.3 dB 1310 nm LC 0.3 dB 1550 nm LC 0.5 dB 1310 nm MTP 0.5 dB 1550 nm MTP
Minimum Return Loss	45 dB 1310 nm LC 45 dB 1550 nm LC 50 dB 1310 nm MTP 50 dB 1550 nm MTP
Fibre Performance	OS2
Optic Fiber Diameter	2 mm
Sheath Type	Metallic cylinder
Condition Of Use	Indoor
Cable Outer Diameter	3.8 mm
Material	Plastic: LC connector
Cable Length	1...500 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Euroclass Level	C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards

Cable specification: IEC 60794-2
Cable test procedure: IEC 60794-1-2
Flame retardance: IEC 60332-1
IEC 60754-1
Acidity of combustion gases: IEC 60754-2
Smoke generation: IEC 61034
LC connector: IEC 61754-20
Performance: ISO/IEC 11801:2011 Ed.2.2
Cabling: ISO/IEC 24764
Fibre cabling test: ISO/IEC 14763-3
TIA/EIA-568-C.3
ANSI/TIA-942
10Gbase-SR: IEEE 802.3ae
MTP connector: IEC 61754-7
MTP connector: TIA/EIA-604-5
Fibre performance: IEC 60793-2-10 Type B1.3
Fibre performance: IEC 60793-2-10 Type B6.A
Fibre performance: ITU G.652.D