

Product data sheet

Specifications



Actassi - equipped 19" fibre optic panel 96 LCq/8x12 MTP - 1U - OS2

VDILP162U5H

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Actassi
Product Or Component Type	Equipped 19" fibre optic panel
Colour	Panel: black (RAL 9005) MTP adapter: black LCq adapter: blue
Quantity Per Set	1

Complementary

Fibre Performance	OS2
Maximum Insertion Loss	MTP: <0.5 dB at 1310 nm LC: <0.3 dB at 1310 nm MTP: <0.5 dB at 1550 nm LC: <0.3 dB at 1550 nm
Minimum Return Loss	50 dB 1310 nm MTP 45 dB 1310 nm LC 50 dB 1550 nm MTP 45 dB 1550 nm LC
Number Of Rack Unit	1U
Termination 1	24 x LC quad
Termination 2	8 x 12 MTP
Condition Of Use	Indoor
Type Of Paint	Panel: epoxy
Material	Sheet steel panel PEI (polyetherimide) MTP adapter PBT (polybutylene terephthalate) LCq adapter
Device Mounting	Flush
Fixing Mode	Cage nut
Height	44 mm
Width	483 mm
Depth	270 mm
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61754-20 LC adapter IEC 50377-7-x LC adapter IEC 61754-7 MTP adapter EN 50377-15-1 MTP adapter TIA/EIA-604-5 MTP adapter ISO/IEC 11801:2011 Ed.2.2 ISO/IEC 24764 ISO/IEC 14763-3 TIA/EIA-568-C.3 ANSI/TIA-942 IEEE 802.3ae 10Gbase-SR
-----------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.7 cm
Package 1 Width	31.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	2.1 kg