

# Product data sheet

Specifications



## Pre Term Copper CL-MLinks UTP Male-Male RJ45 Plug ISO/IEC 11801 Patch Cord Cat 6

VDITBD09D

⚠ Discontinued on: Dec 31, 2010

⚠ Discontinued

### Main

Range	Actassi
Product Name	Actassi CL-MLinks
Product	Pre-terminated link with male-male connectors
Colour	Grey
Cable Shielding Type	U/UTP
Aggregation Types (Customisable Value In Configurator)	Rapstrap polyurethane elastomer black

### Complementary

Type Of Cable	Pre-terminated conforming to ISO 11801: Patch cord Cat6
Number Of Links (Customizable Value In Configurator)	3 6 12 2 1 4
Length (Customizable Value In Configurator)	1...60 m
Communication Network Category	6
Supported Applications	VoIP (Voice IP) PoE+ 30W (Power over Ethernet Plus) PoE 15W (Power over Ethernet) 10GBASE-T
Connector A	RJ45 plug
Connector B	RJ45 plug
Type Of Fanout	Straight
Awg Gauge	AWG 28
Type Of Cable	Patch cord U/UTP
Input Impedance	100 Ohm at 1...250 MHz
Coupling Attenuation	>= 40 dB from 30...100 MHz conforming to IEC 61156-5, ed. 2.1 type III >= 40 - 20 x log10(f / 100) dB from 100...1000 MHz
Bending Radius	Minimum bending radius after installation: 4 x overall diameter Minimum bending radius during installation: 8 x overall diameter
Segregation Class (No Electromagnetic Barrier)	Class b conforming to EN 50174-2
Targeted Region	Europe

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Installation	0...50 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Temperature Resistance	60 °C
Directives	2014/35/EU - low voltage directive
Flame Retardance	LSZH
Standards	EN 50173-1 ISO 11801

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	10 cm
Package 1 Length	4226 cm
Package 1 Weight	15000 g