



### Main

Range of product	Easergy
Product or component type	Voltage presence indicator
Device short name	VPIS V2
Mounting mode	Flush-mounted
Screw type	M3
Standards	IEC 62271-206
Phase concordance unit	VPI62421

### Complementary

Cut-out dimensions	32 x 53 mm
Net weight	0.08 kg
Bulb type	LED
Height	35 mm
Width	70 mm
Depth	40 mm
Mechanical robustness	Impacts de-energized - 2 joules conforming to IEC 61958-1 Impacts de-energized - 3 impacts in the weakest places conforming to IEC 60068-2-75

### Environment

Ambient air temperature for operation	-25...85 °C
Ambient air temperature for storage	-40...85 °C
Electromagnetic compatibility	Electrostatic discharge: (immunity tests-radiated disturbances), criteria B, 8 kV air, 6 kV contact, conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test: (immunity tests-conducted disturbances), criteria A, 10 V/m, 80 MHz...3 GHz, conforming to IEC 61000-4-3 Fast transient bursts: (immunity tests-conducted disturbances), criteria B, 2 kV, conforming to IEC 61000-4-4 Damped oscillatory wave: (immunity tests-conducted disturbances), criteria B, 1 kV, conforming to IEC 61000-4-18

Magnetic field at power frequency: (immunity tests-radiated disturbances), criteria B, 100 A/m, conforming to IEC 61000-4-8  
Immunity to voltage dips: (immunity tests-conducted disturbances), criteria B, 1, conforming to IEC 61000-4-11

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations