

# Product data sheet

Specifications



## safety labels English German, Altivar Process ATV600, Altivar Process ATV900, for Drive Systems

VW3AP0561

### Main

|                                       |                                                                                 |
|---------------------------------------|---------------------------------------------------------------------------------|
| Range Of Product                      | Altivar Process ATV900<br>Altivar Process ATV600                                |
| Accessory / Separate Part Category    | Marked legend                                                                   |
| Accessory / Separate Part Type        | Legend for enclosure                                                            |
| Accessory / Separate Part Destination | Compact drive system                                                            |
| Condition Of Use                      | Cannot be ordered alone, only possible in combination with a standard enclosure |

### Complementary

|                       |                                                                                                                          |
|-----------------------|--------------------------------------------------------------------------------------------------------------------------|
| Product Compatibility | Variable speed drive ATV660<br>Variable speed drive ATV680<br>Variable speed drive ATV960<br>Variable speed drive ATV980 |
|-----------------------|--------------------------------------------------------------------------------------------------------------------------|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 0.9 cm  |
| Package 1 Width              | 1.0 cm  |
| Package 1 Length             | 1.0 cm  |
| Package 1 Weight             | 100.0 g |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications