

# Product data sheet

Specifications



Wear part, fan kit heatsink, variable speed drive, Altivar 61, Altivar 71, Altivar Process 600 900, from 220 to 315kW

VZ3V1212

## Main

|                                    |                                          |
|------------------------------------|------------------------------------------|
| Range Compatibility                | Altivar 61/71<br>Altivar Process 600/900 |
| Accessory / Separate Part Type     | Fan kit                                  |
| Accessory / Separate Part Category | Cooling accessory                        |
| Product Or Component Type          | Fan                                      |
| Net Weight                         | 7.36 kg                                  |

## Complementary

|                       |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Kit Composition       | Fan<br>Mounting bracket<br>Instruction sheet                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Product Compatibility | Variable speed drive ATV61<br>Variable speed drive ATV71<br>Variable speed drive ATV61 Plus<br>Variable speed drive ATV71 Plus<br>Variable speed drive ATV71Q<br>Variable speed drive ATV61Q<br>Variable speed drive ATV630 wall mount 220 kW 380...480 V 1 per drive<br>Variable speed drive ATV630 wall mount 250 kW 380...480 V 2 per drive<br>Variable speed drive ATV630 wall mount 315 kW 380...480 V 3 per drive<br>Variable speed drive ATV930 wall mount 220 kW 380...480 V 1 per drive<br>Variable speed drive ATV930 wall mount 250 kW 380...480 V 2 per drive<br>Variable speed drive ATV930 wall mount 315 kW 380...480 V 3 per drive |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 34 cm    |
| Package 1 Width              | 41 cm    |
| Package 1 Length             | 41 cm    |
| Package 1 Weight             | 7.361 kg |
| Unit Type Of Package 2       | P12      |
| Number Of Units In Package 2 | 12       |
| Package 2 Height             | 105 cm   |
| Package 2 Width              | 80 cm    |
| Package 2 Length             | 120 cm   |
| Package 2 Weight             | 107.5 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications