

# Product data sheet

Specifications



Safety limit switch, Telemecanique  
Safety switches XCS, XCSM, metal,  
rotary lever, 2 NC + 1 NO, cable 1 m

XCSM3715L1

## Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Safety limit switch
Component Name	XCSM
Design	Miniature
Material	Metal
Head Type	Rotary head
Protection Technology	Plastic protective cover, secured by 5-lobe socket head safety screw
Type Of Approach	Lateral approach
Type Of Operator	Thermoplastic roller lever
Contacts Type And Composition	1 NC + 1 NC + 1 NO
Contact Operation	Slow-break, break before make

## Complementary

Electrical Connection	Pre-cabled
Cable Length	1 m
Cable Composition	7 x 0.5 mm <sup>2</sup>
Switch Actuation	By 30° cam
Fixing Mode	By the body
Number Of Poles	3
Positive Opening	With NC contact
Mechanical Durability	10000000 cycles
Minimum Torque For Tripping	0.5 N.m
Positive Opening Minimum Torque	0.1 N.m
Minimum Actuation Speed	6 m/min
Maximum Actuation Speed	1.5 m/s
Contact Code Designation	B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN 60947-5-1 B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN/IEC 60947-5-1 appendix A R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN 60947-5-1 R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1 appendix A
[Ui] Rated Insulation Voltage	300 V conforming to UL 508 400 V (pollution degree 3) conforming to IEC 60947-5-1 300 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60664 4 kV conforming to IEC 60947-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Resistance Across Terminals	25 MOhm conforming to IEC 60255-7 category 3
Short-Circuit Protection	6 A cartridge fuse type gG (gl)
Repeat Accuracy	0.05 mm on the tripping points
Body Material	Zamak
Head Material	Zamak
Depth	34 mm
Height	94 mm
Width	30 mm
Net Weight	0.205 kg

## Environment

Standards	EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-1 UL 508 EN 1088
Product Certifications	UL CSA
Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety Reliability Data	B10d = 50000000 value given for a life time of 20 years limited by mechanical or contact wear
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	25 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	25 gn for 18 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class I conforming to NF C 20-030 Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP68 conforming to IEC 60529
Ik Degree Of Protection	IK06 conforming to EN 50102

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	15 cm
Package 1 Length	20 cm
Package 1 Weight	234 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	25
Package 2 Height	15 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6.624 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	1
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	713 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

California Proposition 65  
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)