

Product data sheet

Specifications



Safety limit switch, Telemecanique Safety switches XCS, plastic, rotary lever, 2NC+1 NO, 1entry tapped M20 x 1.5

XCSP3718P20

! Discontinued

! Discontinued on: Apr 30, 2021

Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Safety limit switch
Component Name	XCSP
Design	Compact
Material	Plastic
Head Type	Rotary head
Protection Technology	Plastic protective cover, secured by 5-lobe socket head safety screw
Type Of Operator	Thermoplastic roller lever
Contacts Type And Composition	1 NC + 1 NC + 1 NO
Contact Operation	Slow-break, break before make
Cable Entry	1 entry tapped for M20 x 1.5

Complementary

Electrical Connection	Terminal
Clamping Connection Capacity	1 x 0.34...2 x 0.75 mm ²
Switch Actuation	By 30° cam
Number Of Poles	3
Positive Opening	With NC contact
Mechanical Durability	10000000 cycles
Minimum Torque For Tripping	0.1 N.m
Positive Opening Minimum Torque	0.25 N.m
Maximum Actuation Speed	1.5 m/s
Contact Code Designation	B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN/IEC 60947-5-1 appendix A R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1 appendix A
[Ithe] Conventional Enclosed Thermal Current	6 A
[Ui] Rated Insulation Voltage	300 V conforming to UL 508 400 V (pollution degree 3) conforming to EN/IEC 60947-1 300 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-1 4 kV conforming to IEC 60664
Maximum Resistance Across Terminals	25 MOhm conforming to IEC 60255-7 category 3

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Short-Circuit Protection	6 A cartridge fuse type gG (gl)
Repeat Accuracy	0.1 mm on tripping points, 1 million operating cycles for head with end plunger
Body Material	Plastic
Head Material	Zamak
Enclosure Material	Plastic
Depth	35 mm
Height	122 mm
Width	34 mm
Net Weight	0.255 kg

Environment

Standards	EN/IEC 60947-5-1 UL 508 EN 1088/ISO 14119 EN/IEC 60204-1 CSA C22.2 No 14
Product Certifications	CSA UL
Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety Reliability Data	B10d = 50000000 value given for a life time of 20 years limited by mechanical or contact wear
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	25 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to NF C 20-030
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529
Ik Degree Of Protection	IK04 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13 cm
Package 1 Width	3.3 cm
Package 1 Length	4.9 cm
Package 1 Weight	147 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
---------------------------	--