


Product data sheet

Specifications



Contact block, Harmony XAC,
double contact, spring return, single
speed, front mounting, snap action,
3NO + 1NO

XESD2241

Main

Range Of Product	Harmony XAC
Product Or Component Type	Contact block
Component Name	XESD
Electrical Circuit Type	Power circuit
Contact Block Application	Single speed
Contact Block Type	Double
Type Of Operator	2 spring return
Product Compatibility	XACB
Mechanical Interlocking	With mechanical interlocking
Contacts Type And Composition	3 NO + 1 NO
Poles Description	3-pole
Mounting Of Block	Front mounting
Contact Operation	Snap action Simultaneous

Complementary

Connections - Terminals	Screw clamp terminals, 1 x 2.5 mm² with or without cable end Screw clamp terminals, 2 x 1.5 mm² with or without cable end
Horizontal Fixing Centres	40 mm
Mechanical Durability	1000000 cycles
[Ithe] Conventional Enclosed Thermal Current	20 A
[Uij] Rated Insulation Voltage	300 V conforming to CSA
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-1
Operating Force	32 N
Short-Circuit Protection	12 A fuse protection by cartridge fuse type aM
Rated Operational Power In W	3000 W AC-3 at 240 V 3000 W AC-4 at 400 V
Rated Power In Hp	3 hp at 240 V
Electrical Durability	1000000 cycles AC-3, 3000 W at 400 V, operating rate <10 cyc/mn, load factor = 0.4 conforming to IEC 60947-3 appendix A 1000000 cycles AC-4, 3000 W at 400 V, operating rate <10 cyc/mn, load factor = 0.4 conforming to IEC 60947-3 appendix A 700000 cycles AC-3, 3000 W at 240 V, operating rate <10 cyc/mn, load factor = 0.4 conforming to IEC 60947-3 appendix A 700000 cycles AC-4, 3000 W at 240 V, operating rate <10 cyc/mn, load factor = 0.4 conforming to IEC 60947-3 appendix A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Terminals Description Iso N°1	B (33-34)NO (43-44)NO (23-24)NO (13-14)NO
Terminals Description Iso N°2	(63-64)NO (44-84)NO (53-54)NO (73-74)NO B
Terminal Identifier	(13-14)NO (11-12)NC
Net Weight	0.21 kg

Environment

Standards	IEC 60947-3 CSA C22.2 No 14 EN 60947-3
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	15 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	100 gn conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 61140

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.5 cm
Package 1 Length	10.0 cm
Package 1 Weight	275.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65		WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov