

Product data sheet

Specifications



module XPSBAE - two - hand control IIIA - 115 - 230 V AC

XPSBAE3920P

⚠ Discontinued on: Jun 30, 2021

⚠ To be end-of-service on: Dec 31, 2025

⚠ Discontinued - Service only

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSBAE
Safety Module Application	For electrical monitoring of two-hand control stations
Function Of Module	Monitoring two-hand control station type IIIA
Safety Level	Can reach PL c/category 1 conforming to EN/ISO 13849-1 Can reach SILCL 1 conforming to EN/IEC 62061
Safety Reliability Data	MTTFd = 55 years conforming to EN/ISO 13849-1 PFHd = 2.1E-6 1/h conforming to EN/IEC 62061
Connections - Terminals	Captive screw clamp terminals, 1 x 0.25...1 x 1.5 mm ² flexible with cable end, with bezel Captive screw clamp terminals, 1 x 0.25...1 x 2.5 mm ² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.25...2 x 1 mm ² flexible with cable end, without bezel Captive screw clamp terminals, 2 x 0.5...2 x 1.5 mm ² flexible with cable end, with double bezel Captive screw clamp terminals, 1 x 0.2...1 x 2.5 mm ² stranded without cable end Captive screw clamp terminals, 1 x 0.2...1 x 2.5 mm ² solid without cable end Captive screw clamp terminals, 2 x 0.2...2 x 1.5 mm ² stranded without cable end Captive screw clamp terminals, 2 x 0.2...2 x 1 mm ² solid without cable end
Output Type	Relay, 1 NO circuit(s), volt-free
Number Of Additional Circuits	1 NC
[Us] Rated Supply Voltage	115...230 V AC - 15...10 %

Complementary

Synchronisation Time Between Inputs	0.5 s
Supply Frequency	50/60 Hz
Power Consumption In Va	3.3 VA
Input Protection Type	Internal, electronic
Number Of Inputs	1 NC + NO
Input Current	2.5 mA NC 25 mA NO
Input Compatibility	Two-hand control conforming to EN 574
[Uc] Control Circuit Voltage	24 V DC
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Breaking Capacity	3 A at 24 V (DC-13) time constant: 20 ms for relay output
[Ith] Conventional Free Air Thermal Current	5 A
Associated Fuse Rating	4 A gG for relay output conforming to EN/IEC 60947-5-1 6 A fast blow
Minimum Output Current	10 mA for relay output
Minimum Output Voltage	17 V for relay output
Maximum Response Time On Input Open	20 ms
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local Signalling	2 LEDs
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.1 kg

Environment

Standards	EN 574 type III A EN 62061 EN/IEC 60947-5-1 EN 60947-01 EN/ISO 13849-1 EN/IEC 60204-1
Product Certifications	CSA UL TÜV
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-25...75 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	11.2 cm
Package 1 Length	12.4 cm
Package 1 Weight	176 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.85 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions

