

# Product data sheet

Specifications



inductive sensor XS1 M18, L50mm,  
brass, Sn8mm, 12..24VDC, M12

XS118B3NAM12

## Main

Range Of Product	Telemecanique Inductive proximity sensors XS
Series Name	General purpose
Sensor Type	Inductive proximity sensor
Device Application	Mobile equipment
Sensor Name	XS1
Sensor Design	Cylindrical M18
Size	50 mm
Body Type	Fixed
Detector Flush Mounting Acceptance	Flush mountable
Material	Metal
Type Of Output Signal	Discrete
Wiring Technique	3-wire
[Sn] Nominal Sensing Distance	8 mm
Discrete Output Function	1 NO
Output Circuit Type	DC
Discrete Output Type	NPN
Electrical Connection	Male connector M12, 4 pins
[Us] Rated Supply Voltage	12...24 V DC with reverse polarity protection
Switching Capacity In Ma	<= 200 mA with overload and short-circuit protection
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP67 conforming to IEC 60529

## Complementary

Thread Type	M18 x 1
Detection Face	Frontal
Front Material	PPS
Enclosure Material	Nickel plated brass
Operating Zone	0...6.4 mm
Differential Travel	1...15% of Sr
Status Led	Output state: 1 LED (yellow)
Supply Voltage Limits	10...36 V DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Switching Frequency	<= 1000 Hz
Maximum Voltage Drop	<2 V (closed)
Current Consumption	<= 10 mA no-load
Maximum Delay First Up	10 ms
Maximum Delay Response	0.3 ms
Maximum Delay Recovery	0.7 ms
Marking	CE
Threaded Length	28 mm
Length	50 mm

## Environment

Product Certifications	CSA E2 UL
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Vibration Resistance	25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	4.2 cm
Package 1 Length	9.5 cm
Package 1 Weight	57 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)


Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

Circularity Profile [End of Life Information](#)

California Proposition 65  
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Dimensions Drawings

Dimensions




(1) : LED

Mounting and Clearance


Minimum Mounting Distances

Side by side




$e\ (1) \geq 16\text{ mm}/0.63\text{ in.}$

Face to face



$e\ (2) \geq 100\text{ mm}/3.94\text{ in.}$

Facing a metal object




$e\ (3) \geq 25\text{ mm}/0.98\text{ in}$

Connections and Schema

Wiring Schemes

M12 connector



NPN

