

# Product data sheet

Specifications



## plastic key operated solenoid switch XCSLE - 2NC+2NO - slow - M23 connect. - 24V

XCSLE252531M2

 **Discontinued on:** Jan 4, 2022

 **Discontinued**

### Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Safety switch
Component Name	XCSLE
Design	Slim
Material	Plastic
Head Type	Key operated turret head
Contacts Type And Composition	1 NC + 1 NO
Contact Operation	Slow-break, break before make
Solenoid Contacts Type And Composition	1 NC + 1 NO (slow-break, break before make)
Electromagnet Interlocking	Locking on de-energisation and unlocking on energisation of solenoid
[Us] Solenoid Rated Supply Voltage	24 V - 15...10 %
Cable Outer Diameter	7...13 mm
Electrical Connection	Male connector M23, 16 pins
Number Of Poles	2
Locking Options Description	With interlocking, locking by solenoid
Local Signalling	1 LED (orange) for actuator withdrawn 1 LED (green) for actuator inserted and locked
Signalling Circuit Voltage	24 V

### Complementary

Positive Opening	With NC contact
Supply Voltage Type	AC/DC
Supply Frequency	50/60 Hz
Load Factor	1
Signalling Circuit Type	AC/DC
Mechanical Durability	1000000 cycles
Minimum Actuation Speed	0.01 m/s
Maximum Actuation Speed	0.5 m/s
[Ie] Rated Operational Current	1.5 A at 24 V 0.22 A at 24 V
[Ithe] Conventional Enclosed Thermal Current	4 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Load Current	<= 15 A
[Ui] Rated Insulation Voltage	60 V (pollution degree 3) conforming to EN/IEC 60947-1 50 V conforming to UL 508 50 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	0.8 kV conforming to EN/IEC 60947-5-1
Minimum Switching Current	10 mA at 20 °C
Minimum Switching Voltage	17 V
Short-Circuit Protection	4 A cartridge fuse type gG (gl) 6 A type fast blow
Maximum Actuator Forcible Withdrawal Rtc	1400 N
Minimum Actuator Force For Extraction	20 N
Resistance To Mechanical Impact	1.2 J against the partition 4.9 J without partition
Maximum Operating Rate	10 cyc/mn for maximum durability
Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 conforming to EN/IEC 61508
Safety Reliability Data	B10d = 5500000 value given for a life time of 20 years limited by mechanical or contact wear
Body Material	PA (polyamide)
Head Material	PA (polyamide)
Depth	51 mm
Height	225 mm
Width	44 mm
Net Weight	0.53 kg

## Environment

Standards	EN/IEC 62061 EN/IEC 60947-5-1 CSA C22.2 No 14 EN/IEC 60204-1 EN/ISO 13849-1 EN 1088/ISO 14119 UL 508
Product Certifications	UL CSA TÜV
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	5 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	10 gn for 11 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class III conforming to EN/IEC 61140
Ip Degree Of Protection	IP65 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 IP65

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	7.5 cm
Package 1 Length	24.2 cm
Package 1 Weight	660 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---

California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
---------------------------	--