

# Product data sheet

Specifications



Safety switch, Telemecanique  
Safety switches XCS, metal XCSLF,  
4 NC+2 NO, slow break, 3 entries  
tapped M20, 24 V

XCSLF3737412

## Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Safety switch
Component Name	XCSLF
Design	Slim
Material	Metal
Head Type	Key operated turret head
Contacts Type And Composition	2 NC + 1 NO
Contact Operation	Slow-break, break before make
Solenoid Contacts Type And Composition	2 NC + 1 NO (slow-break, break before make)
Cable Entry	3 entries tapped for M20 x 1.5
Electromagnet Interlocking	Locking on de-energisation and unlocking on energisation of solenoid By mushroom head push-button turn to release for escape release
[Us] Solenoid Rated Supply Voltage	24 V - 15...10 %
Cable Outer Diameter	7...13 mm
Electrical Connection	Spring terminal, clamping capacity: 1 x 1.5 mm² flexible or solid cable Spring terminal, clamping capacity: 2 x 0.5 mm² flexible cables with 13 mm bared ends
Number Of Poles	3
Locking Options Description	With interlocking, locking by solenoid
Local Signalling	1 LED (orange) for actuator withdrawn 1 LED (green) for actuator inserted and locked
Signalling Circuit Voltage	24 V

## Complementary

Positive Opening	With NC contact
Supply Voltage Type	AC/DC
Supply Frequency	50/60 Hz
Load Factor	1
Signalling Circuit Type	AC/DC
Mechanical Durability	30000 cycles
Minimum Actuation Speed	0.01 m/s
Maximum Actuation Speed	0.5 m/s

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ie] Rated Operational Current	0.55 A at 24 V, DC-13, R300 conforming to IEC 60947-5-1 0.75 A at 240 V, AC-15, C300 conforming to IEC 60947-5-1
[Ithe] Conventional Enclosed Thermal Current	4 A
Maximum Load Current	<= 15 A
[Ui] Rated Insulation Voltage	300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14 250 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-5-1
Minimum Switching Current	10 mA at 20 °C
Minimum Switching Voltage	17 V
Short-Circuit Protection	4 A cartridge fuse type gG (gl) 6 A type fast blow
Maximum Actuator Forcible Withdrawal Rtc	3000 N
Minimum Actuator Force For Extraction	20 N
Resistance To Mechanical Impact	9.6 J against the partition 6.4 J without partition
Maximum Operating Rate	10 cyc/mn for maximum durability
Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to ISO 13849-1 Can reach SIL 3 conforming to IEC 61508
Safety Reliability Data	B10d = 5500000 value given for a life time of 20 years limited by mechanical or contact wear
Body Material	Zamak
Head Material	Zamak
Depth	113 mm
Height	205 mm
Width	44 mm
Net Weight	1.2 kg

## Environment

Standards	UL 508 EN 1088/ISO 14119 IEC 62061 IEC 60204-1 CSA C22.2 No 14 IEC 60947-5-1 ISO 13849-1
Product Certifications	CSA TÜV UL
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	5 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	10 gn for 11 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class I conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to EN/IEC 60529 and EN/IEC 60947-5-1

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.8 cm
Package 1 Width	14.5 cm
Package 1 Length	22.5 cm
Package 1 Weight	1.406 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	4
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.451 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	64
Package 3 Height	60.0 cm
Package 3 Width	80.0 cm
Package 3 Length	64.0 cm
Package 3 Weight	92.416 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

California Proposition 65  
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)