

Product data sheet

Specifications



Guard switch, Telemecanique Safety switches XCS, XCSPL, elbowed flush lever, to left, 2NC, M16

XCSPL792

Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Guard switch
Component Name	XCSPL
Material	Plastic
Head Type	Turret head rotary lever
Insulation	Double insulated
Type Of Operator	Elbowed flush lever
Operator Direction Information	To left
Electrical Connection	Terminal
Contacts Type And Composition	1 NC + 1 NC
Contact Operation	Slow-break
Clamping Connection Capacity	1 x 0.5...2 x 1.5 mm ² with or without cable end
Cable Entry	1 entry tapped for M16 x 1.5
Number Of Poles	2

Complementary

Cable Outer Diameter	7...10 mm
Positive Opening	With NC contact
Tripping Angle	5 °
Mechanical Durability	1000000 cycles
Minimum Torque For Tripping	0.1 N.m
Positive Opening Minimum Torque	0.25 N.m
Contact Code Designation	A300, AC-15 (Ue = 120 V, Ie = 6 A) conforming to EN/IEC 60947-5-1 A300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (Ue = 125 V, Ie = 0.55 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to EN/IEC 60947-5-1
[Ithe] Conventional Enclosed Thermal Current	10 A
[Ui] Rated Insulation Voltage	300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14 500 V (pollution degree 3) conforming to EN/IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-5-1
Maximum Resistance Across Terminals	30 mOhm conforming to EN/IEC 60947-5-4
Short-Circuit Protection	10 A cartridge fuse type gG (gl)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety Reliability Data	B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear
Enclosure Material	Polyamide PA66 fibre glass impregnated
Lever Material	Stainless steel
Width	103 mm
Height	88 mm
Depth	30 mm
Net Weight	0.095 kg

Environment

Standards	EN/ISO 12100 EN 1088/ISO 14119 EN/IEC 60204-1 EN/IEC 60947-5-4 EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508
Product Certifications	BG UL CSA
Protective Treatment	TC TH
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	50 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to EN/IEC 61140
Ip Degree Of Protection	IP67 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	20.500 cm
Package 1 Length	4.000 cm
Package 1 Weight	129.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	1.756 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov