

Product data sheet

Specifications



Guard switch, Telemecanique Safety switches XCS, XCSPR, spindle 30 mm, 2NC, Pg11

XCSPR751

Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Guard switch
Component Name	XCSPR
Material	Plastic
Head Type	Turret head rotary axis
Insulation	Double insulated
Type Of Operator	Spindle 30 mm
Electrical Connection	Terminal
Contacts Type And Composition	1 NC + 1 NC
Contact Operation	Slow-break
Clamping Connection Capacity	1 x 0.5...2 x 1.5 mm ² with or without cable end
Cable Entry	1 entry tapped for Pg 11
Number Of Poles	2

Complementary

Cable Outer Diameter	7...10 mm
Positive Opening	With NC contact
Tripping Angle	5 °
Mechanical Durability	1000000 cycles
Minimum Torque For Tripping	0.1 N.m
Positive Opening Minimum Torque	0.25 N.m
Contact Code Designation	A300, AC-15 (Ue = 120 V, Ie = 6 A) conforming to IEC 60947-5-1 A300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to IEC 60947-5-1 Q300, DC-13 (Ue = 125 V, Ie = 0.55 A) conforming to IEC 60947-5-1 Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to IEC 60947-5-1
[Ithe] Conventional Enclosed Thermal Current	10 A
[Ui] Rated Insulation Voltage	300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14 500 V (pollution degree 3) conforming to IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-5-1
Maximum Resistance Across Terminals	30 mOhm conforming to IEC 60947-5-4
Short-Circuit Protection	10 A cartridge fuse type gG (gl)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety Reliability Data	B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear
Enclosure Material	Polyamide PA66 fibre glass impregnated
Lever Material	Stainless steel
Width	30 mm
Height	96 mm
Depth	60 mm
Net Weight	0.105 kg

Environment

Standards	IEC 60947-5-4 IEC 60204-1 CSA C22.2 No 14 ISO 12100 EN 1088/ISO 14119 IEC 60947-5-1 UL 508
Product Certifications	CSA UL BG
Protective Treatment	TC TH
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	50 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP67 conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	11.4 cm
Package 1 Length	11.4 cm
Package 1 Weight	137.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	18
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.754 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov