

# Product data sheet

## Characteristics

# XS7T4DA210TT

inductive sensor XS7 40x40x40 - plastic -  
Sn15mm - 12..48VDC - cable 2m



### Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS7
Sensor design	Cubic form 40 x 40 x 40
Size	40 mm
Body type	Fixed
Detector flush mounting acceptance	Flush mountable
Material	Plastic
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	15 mm
Discrete output function	1 NO
Output circuit type	DC
Electrical connection	Cable
Cable length	2 m
[Us] rated supply voltage	12...48 V DC with reverse polarity protection
Switching capacity in mA	1.5...100 mA with overload and short-circuit protection
IP degree of protection	IP67 conforming to IEC 60529

### Complementary

Front material	Plastic
Operating zone	0...12 mm
Differential travel	3...20% of Sr
Repeat accuracy	<= 3% of Sr
Cable composition	2 x 0.5 mm <sup>2</sup>
Wire insulation material	PVC
Status LED	1 LED (yellow) for output state
Supply voltage limits	10...58 V DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Residual current	<= 0.7 mA, open state
Switching frequency	<= 150 Hz
Voltage drop	<= 5.2 V, closed state
Delay first up	<= 5 ms
Delay response	<= 2 ms
Delay recovery	<= 5 ms
Marking	CE
Depth	40 mm
Height	40 mm
Width	40 mm

## Environment

Product certifications	CCC CSA UL
Ambient air temperature for operation	-25...85 °C

## Contractual warranty

Warranty period	18 months
-----------------	-----------