



## Main

Range of product	Preventa Safety detection
Product or component type	Safety light curtains transmitter type 4
Series name	Optimum
Device short name	XUSLB
Product compatibility	XUSLBR5A0880
Product specific application	For hand protection
Minimum object diameter for detection	30 mm
[Sn] nominal sensing distance	8 m with PDM 0.3...20 m
Height protected	880 mm
Number of beams	44

## Complementary

Detection system	Transmitter-receiver system
Response time	23 ms
[EAA] effective aperture angle	2.5 ° at 3 m
Light source	GaAIAs LED, 880 nm
[Us] rated supply voltage	24 V DC (+/- 20 %) against reverse polarity
[Ie] rated operational current	2 A
Current consumption	285 mA
Monitoring act of of relay MPCE/EDM	50 mA
Local signalling	1 LED power supply
Electrical connection	1 female connector M12 5 pins
Marking	CE
Material	Casing : aluminium End caps : 20 % fibre glass impregnated nylon
Fixing mode	End brackets

## Environment

Standards	EMC 2004/108/EC EN/IEC 61496-2 OSHA 1910-212
-----------	--

OSHA 1910-217C  
EN/IEC 61496-1  
Machinery directive 2006/42/EC  
EN/IEC 61496-1-2 for type 4 ESPE  
ANSI/RIA R15.06  
ROHS directive 2002/95/EC  
Work equipment directive 2009/104/EC  
ANSI B11:19-1990

Product certifications	UL CSA TÜV
Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-25...75 °C
Relative humidity	0...95 % without condensation
IP degree of protection	IP65
Shock resistance	10 gn for 16 ms conforming to IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm (f = 10...55 Hz) conforming to IEC 61496-1

### Contractual warranty

Warranty period	18 months
-----------------	-----------