



Main

Range of product	Preventa Safety automation
Product or component type	Preventa safety PLC compact
Safety module name	XPSMF40
Safety module application	F use with numerous machine safety functions and for the protection of personnel
Safety use category	Category 4 maximum conforming to EN 954-1 Performance level e conforming to EN/ISO 13849-1 SIL 3 conforming to EN/IEC 61508
Structure type	10BASE-T/100BASE-TX Modbus TCP/IP 10BASE-T/100BASE-TX safe Ethernet

Complementary

Function of module	Monitoring safety actuators discrete output Monitoring safety detection discrete input Monitoring safety dialogue discrete input Monitoring safety dialogue discrete output Monitoring short-circuit and line break line control outputs
[Us] rated supply voltage	24 V DC (- 15...20 %)
Supply	SELV or PELV conforming to EN/IEC 60950
No load current	0.5 A
Protection type	10 A internal fuse
Clock	With, supplied by backup capacitor for 1 week following loss of supply
Response time	Depending on size of application
Memory description	User logic 250 kB for application User logic 250 kB for data
Group of channels	2 groups of 4 line control outputs
Discrete I/O number	24 configurable
Discrete input number	<= 24, not isolated
Voltage state 0 guaranteed	<= 24 V for discrete input
Voltage state 1 guaranteed	24...30 V for discrete input
Current state 0 guaranteed	<= 1.5 mA, discrete input
Current state 1 guaranteed	3.5...4.5 mA, discrete input
Discrete input voltage	20 V
Discrete input current	100 mA
Input resistance	<= 7 kOhm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input overvoltage protection	-10...35 V for discrete input
Discrete output number	<= 24, not isolated
Discrete output voltage	24 V DC
Output voltage tolerance	+/- 2 %
Discrete output current	<= 7 A (all channels) 1 A at 60 °C (channels 4, 8, 12, 16, 20 and 24) 2 A at 50 °C (channels 4, 8, 12, 16, 20 and 24) 0.5 A at 60 °C (channels 1 to 3, 5 to 7, 9 to 11, 13 to 15, 17 to 19, 21 to 23)
Minimum load	2 mA per discrete output
Leakage current	<= 1 mA, at 2 V at state 0 for discrete output
Overload protection	Shutdown of outputs concerned with cyclic reconnection
Output voltage	20 V line control outputs
Nominal output current	60 mA for line control outputs
Communication port protocol	Modbus TCP/IP with 2 RJ45 port(s), transmission rate: 100 Mbps, 10 Mbps, medium: dual twisted pair cable, category 5D or better Safe Ethernet with 2 RJ45 port(s), transmission rate: 100 Mbps, 10 Mbps, medium: dual twisted pair cable, category 5D or better Modbus RTU with 1 RJ45 port(s), RS485, medium: shielded dual twisted pair cable
Exchange mode	Half duplex, full duplex, autonegotiation Modbus TCP/IP Half duplex, full duplex, autonegotiation safe Ethernet
Method of access	Slave Modbus TCP/IP Slave V0 Modbus serial
Number of addresses	122 Modbus serial
Concept	Transparent Ready Modbus TCP/IP
Web server	Class A10 Modbus TCP/IP
Web services	Modbus identification request Modbus TCP/IP Modbus TCP/IP messaging (reading/writing of data words) Modbus TCP/IP Modbus TCP/IP server Modbus TCP/IP Standard 502 Modbus TCP/IP
Maximum number of connections	1 to 20, Modbus TCP/IP
Operating distance	<= 300 m (between station) discrete input <= 300 m (between station) discrete output
Number of terminal blocks	1 for power supply 2 for line control outputs 6 for discrete input/output circuit 8 for line control outputs
Connections - terminals	Captive spring terminals, clamping capacity: 1 x 0.25...1 x 0.34 mm ² , AWG 22 flexible without cable end for discrete input/output circuit Captive spring terminals, clamping capacity: 1 x 0.25...1 x 0.34 mm ² , AWG 22 flexible without cable end for line control outputs Captive screw clamp terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm ² , AWG 25...AWG 15 solid without cable end for discrete input/output circuit Captive screw clamp terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm ² , AWG 25...AWG 15 solid without cable end for line control outputs Captive screw clamp terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm ² , AWG 28...AWG 16 flexible without cable end for discrete input/output circuit Captive screw clamp terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm ² , AWG 28...AWG 16 flexible without cable end for line control outputs Captive screw clamp terminals, clamping capacity: 1 x 0.2...1 x 2.5 mm ² , AWG 24...AWG 12 flexible without cable end for power supply Captive screw clamp terminals, clamping capacity: 1 x 0.2...1 x 2.5 mm ² , AWG 24...AWG 12 solid without cable end for power supply Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 0.5 mm ² , AWG 23...AWG 20 flexible with cable end for discrete input/output circuit Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 0.5 mm ² , AWG 23...AWG 20 flexible with cable end for line control outputs Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 1.5 mm ² , AWG 23...AWG 15 flexible without cable end for discrete input/output circuit Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 1.5 mm ² , AWG 23...AWG 15 flexible without cable end for line control outputs Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 2.5 mm ² , AWG 23...AWG 14 flexible with cable end for power supply Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 2.5 mm ² , AWG 23...AWG 14 flexible without cable end for power supply Captive spring terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm ² , AWG 26...AWG 16 solid without cable end for discrete input/output circuit

Captive spring terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm², AWG 26...AWG 16 solid without cable end for line control outputs
 Captive spring terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm², AWG 26...AWG 17 flexible without cable end for discrete input/output circuit
 Captive spring terminals, clamping capacity: 1 x 0.14...1 x 1.5 mm², AWG 26...AWG 17 flexible without cable end for line control outputs
 Captive spring terminals, clamping capacity: 1 x 0.2...1 x 2.5 mm², AWG 24...AWG 12 flexible without cable end for power supply
 Captive spring terminals, clamping capacity: 1 x 0.2...1 x 2.5 mm², AWG 24...AWG 12 solid without cable end for power supply
 Captive spring terminals, clamping capacity: 1 x 0.25...1 x 2.5 mm², AWG 23...AWG 12 flexible with cable end for power supply
 Captive spring terminals, clamping capacity: 1 x 0.25...1 x 2.5 mm², AWG 23...AWG 12 flexible without cable end for power supply
 Captive spring terminals, clamping capacity: 1 x 0.5 mm², AWG 20 flexible with cable end for discrete input/output circuit
 Captive spring terminals, clamping capacity: 1 x 0.5 mm², AWG 20 flexible with cable end for line control outputs

Tightening torque	0.22...0.25 N.m for discrete input/output circuit captive screw clamp terminals 0.22...0.25 N.m for line control outputs captive screw clamp terminals 0.5 N.m for power supply captive screw clamp terminals
Wire stripping length	10 mm for power supply captive screw clamp terminals 9 mm for discrete input/output circuit captive screw clamp terminals 9 mm for discrete input/output circuit captive spring terminals 9 mm for line control outputs captive screw clamp terminals 9 mm for line control outputs captive spring terminals 9 mm for power supply captive spring terminals
Current consumption	8 A at 24 V DC on power supply
Mounting support	35 mm symmetrical DIN rail
Depth	153 mm
Height	151.5 mm
Width	74 mm
Product weight	1 kg

Environment

Standards	EN 50156-1 : 2004 NFPA 72 : 2002 NFPA 85 : 2001 IEC 61511 part 1-3 : 2004 EN 230 : 1990 EN/IEC 61131-2 : 2003 EN 54-2 : 1997 DIN VDE 0116 : 1989 EN 61000-6-2 : 2001 EN 12067-2 : 2004 EN 298 : 2003 EN 61000-6-4 : 2001
Immunity to microbreaks	10 ms
IP degree of protection	IP20 (enclosure)
Ambient air temperature for operation	0...60 °C conforming to EN 61131-2
Ambient air temperature for storage	-40...85 °C conforming to EN 61131-2
Relative humidity	95 % (supply not connected)
Operating altitude	< 2000 m
Pollution degree	2
Electrical shock protection class	Class II conforming to IEC 61131-2
Electromagnetic compatibility	EN/IEC 61131-2
Vibration resistance	1 gn (f = 9...150 Hz) conforming to EN 61131-2
Shock resistance	15 gn for 11 ms conforming to EN 61131-2
Resistance to electrostatic discharge	4 kV contact conforming to EN/IEC 61000-4-2 8 kV on air conforming to EN/IEC 61000-4-2
Resistance to electromagnetic fields	10 V/m (80...2000 MHz), amplitude modulation 80 % conforming to EN/IEC 61000-4-3

Contractual warranty

Warranty period	18 months
-----------------	-----------
