



Main

Range of product	Preventa Safety detection
Product or component type	Safety light curtains transmitter type 4
Device short name	XUSLP
Product compatibility	XUSLPZ3A0500B
Design	Compact
Product specific application	For body protection
Minimum object diameter for detection	500 mm
[Sn] nominal sensing distance	0.8...20 m depending on configuration 0.8...70 m depending on configuration
Height protected	300 mm
Number of beams	3

Complementary

Detection system	Transmitter-receiver system
Response time	< 16 ms light beam coding C < 20 ms light beam coding B < 24 ms light beam coding A
[EAA] effective aperture angle	2.5 ° at 3 m
Light source	GaAIAs LED, 850 nm
[Us] rated supply voltage	24 V DC (+/- 20 %) against reverse polarity
[Ie] rated operational current	2 A
Current consumption	100 mA
Monitoring act of of relay MPCE/EDM	50 mA
Local signalling	2 LEDs power supply, diagnostic
Electrical connection	Terminal block
Marking	CE
Material	Casing : aluminium End caps : 20 % fibre glass impregnated nylon Front face : acrylic
Fixing mode	End brackets

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	ANSI B11:19-1990 ANSI/RIA R15.06 EN/IEC 61496-1 EN/IEC 61496-1-2 for type 4 ESPE EN/IEC 61496-2 OSHA 1910-212 OSHA 1910-217C ROHS directive 2002/95/EC Machinery directive 2006/42/EC EMC 2004/108/EC Work equipment directive 2009/104/EC
Product certifications	CSA TÜV UL
Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-25...75 °C
Relative humidity	0...95 % without condensation
IP degree of protection	IP65 IP67
Shock resistance	10 gn for 16 ms conforming to IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm (f = 10...55 Hz) conforming to IEC 61496-1

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0730 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------