



## Main

Range of product	OsiSense XU
Series name	Application, conveyor system and access control
Electronic sensor type	Photo-electric sensor
Sensor name	XUY
Sensor design	Compact
Detection system	Diffuse
Material	Plastic
Type of output signal	Discrete
Discrete output type	Relay
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Screw terminal
Product specific application	Detection of belt breakage Materials handling Access control
Emission	Infrared
[Sn] nominal sensing distance	1.5 m

## Complementary

Enclosure material	Polycarbonate
Output type	Relay
Status LED	1 LED color: green for output status 1 LED color: red for alignment assistance 1 LED color: red for dirty optics 1 LED color: red for limit of detection 1 LED color: red for time delay 1 LED color: red for time function indicator
Supply voltage limits	10...30 V DC
Switching capacity in mA	3 A
Switching frequency	> 25 Hz
Maximum voltage drop	<2 V at 100 mA (closed state) <1 V at 10 mA (closed state)
Power consumption in VA	2 VA no load
Time delay range	0...10 s retriggerable delay for output circuit
Setting-up	Teach mode and/or fine manual adjustment

---

Net weight	0.15 kg
------------	---------

---

## Environment

---

Product certifications	CE
Ambient air temperature for operation	0...60 °C
Ambient air temperature for storage	-20...80 °C
Immunity to ambient light	10000 lux incandescent bulb at 5° of optical axis 20000 lux natural light at 5° to the optical axis
IP degree of protection	IP65 conforming to IEC 60529 IP67 conforming to IEC 60529

---

## Offer Sustainability

---

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

---

## Contractual warranty

---

Warranty	18 months
----------	-----------

---