

Product data sheet

Specifications



XR, monobloc sprocket with through hub, 12.7 mm pitch, 16 teeth, shaft Ø 50

XR2AZ31625

⚠ Discontinued on: Jan 16, 2023

⚠ Discontinued

Main

Range Of Product	XR
Accessory / Separate Part Designation	Monobloc sprocket with through hub
Accessory / Separate Part Type	Winch shaft chain sprocket
Accessory / Separate Part Category	Separate parts
Accessory / Separate Part Destination	Screw limit switch

Complementary

Number Of Teeth	16
Chain Pitch	12.7 mm
Bore Diameter For Shaft	0...25 mm
Shaft Diameter	50 mm
External Diameter	73 mm
Pinion Length	35 mm

Environment

Standards	NF E 23-111
-----------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.0 cm
Package 1 Length	7.0 cm
Package 1 Weight	424.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov