

# Product data sheet

Specifications



## SINGLE TONE SOUNDER UNIT 12 - 48VAC/DC

XVEC9B

⚠ Discontinued on: Jun 30, 2015

⚠ End-of-service on: Dec 31, 2015

⚠ Discontinued

### Main

Range Of Product	Harmony XVE Optimum
Product Or Component Type	Indicator bank
Beacon Or Indicator Bank Unit Type	Audible unit
Signalling Type	Continuous buzzer, single tone
Component Name	XVE
[Us] Rated Supply Voltage	24 V AC/DC

### Complementary

Mounting Diameter	70 mm
Assembly Style	Customer assembly
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm <sup>2</sup> with cable end
Marking	CE
Current Consumption	< 15 mA
Fundamental Frequency	2.6 kHz
Cad Overall Width	70 mm
Cad Overall Height	52 mm
Cad Overall Depth	70 mm
Net Weight	0.09 kg

### Environment

Noise Level	85 dB at 1 m
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Product Certifications	CCC CSA UL
Ambient Air Temperature For Operation	-40...70 °C
Ambient Air Temperature For Storage	-25...55 °C
Electrical Shock Protection Class	Class I aluminium tube mounting conforming to IEC 61140 Class I plastic tube mounting conforming to IEC 61140
Protective Treatment	TC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Ip Degree Of Protection</b>	IP40 any position except vertical position conforming to IEC 60529 IP42 vertical position conforming to IEC 60529
--------------------------------	--

## Contractual warranty


<b>Warranty</b>	18 months
-----------------	-----------

Dimensions Drawings

Indicator Bank

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



- (1) Cover (supplied with base unit XVEC21/C21P)
- (2) Illuminated or audible unit
- (3) Base unit XVEC21/C21P, to be ordered separately
- (4) Fixing base, to be ordered separately

Number of units (ref. 2)	b in mm	b in in.
1 unit	111	4.37
2 units	163	6.42
3 units	215	8.46
4 units	267	10.51
5 units	319	12.56