

# Product data sheet

Specifications



inductive sensor XS1 M30, L55mm,  
brass, Sn15mm, 12..24VDC, M12

XS130B3PAM12

## Main

Range Of Product	Telemecanique Inductive proximity sensors XS
Series Name	General purpose
Sensor Type	Inductive proximity sensor
Device Application	Mobile equipment
Sensor Name	XS1
Sensor Design	Cylindrical M30
Size	55 mm
Body Type	Fixed
Detector Flush Mounting Acceptance	Flush mountable
Material	Metal
Type Of Output Signal	Discrete
Wiring Technique	3-wire
[Sn] Nominal Sensing Distance	15 mm
Discrete Output Function	1 NO
Output Circuit Type	DC
Discrete Output Type	PNP
Electrical Connection	Male connector M12, 4 pins
[Us] Rated Supply Voltage	12...24 V DC with reverse polarity protection
Switching Capacity In Ma	<= 200 mA with overload and short-circuit protection
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP67 conforming to IEC 60529

## Complementary

Thread Type	M30 x 1.5
Detection Face	Frontal
Front Material	PPS
Enclosure Material	Nickel plated brass
Operating Zone	0...12 mm
Differential Travel	1...15% of Sr
Status Led	Output state: 1 LED (yellow)
Supply Voltage Limits	10...36 V DC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Switching Frequency	<= 500 Hz
Maximum Voltage Drop	<2 V (closed)
Current Consumption	<= 10 mA no-load
Maximum Delay First Up	10 ms
Maximum Delay Response	0.6 ms
Maximum Delay Recovery	1.4 ms
Marking	CE
Threaded Length	32 mm
Length	55 mm
Net Weight	0.13 kg

## Environment

Product Certifications	E2 UL CSA
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Vibration Resistance	25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.200 cm
Package 1 Width	9.600 cm
Package 1 Length	6.600 cm
Package 1 Weight	118.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	22
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.890 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)


Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

Circularity Profile [End of Life Information](#)

California Proposition 65  
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Dimensions Drawings

Dimensions




(1) : LED

Mounting and Clearance


Minimum Mounting Distances

Side by side




$e (1) \geq 30 \text{ mm}/1.18 \text{ in.}$

Face to face



$e (2) \geq 180 \text{ mm}/7.09 \text{ in.}$

Facing a metal object




$e (3) \geq 45 \text{ mm}/1.77 \text{ in.}$


Connections and Schema

Wiring Schemes

M12 connector



PNP



- 1 : (+)
- 2 : Not connected
- 3 : (-)
- 4 : NO Output