



ⓘ Discontinued

Commercial status

Discontinued: 30 June 2015

End-of-service: 31 December 2015

Main

Range of product	Harmony XVP Universal
Product or component type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit with cream clamping ring
Signalling type	Flashing
Mounting diameter	50 mm
Component name	XVPC
Material	Polycarbonate and polyamide
Light source	Integral flash discharge tube, blue
Bulb type	Flash discharge tube
[Us] rated supply voltage	230 V AC
Flash energy	0.6 J

Complementary

Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals, $\leq 1 \times 1.5 \text{ mm}^2$ with cable end
Marking	CE
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 U_n conforming to IEC 60947-5-1
Current consumption	$\leq 11 \text{ mA AC}$
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1
Flashing frequency	0.6...2 Hz
Service life in hours	1000 h at $-25...50 \text{ }^\circ\text{C}$
CAD overall width	56 mm
CAD overall height	65 mm
CAD overall depth	56 mm
Net weight	0.115 kg

Environment

Product certifications	CULus
Standards	EN/IEC 60947-5-1
Protective treatment	TC

Ambient air temperature for storage	-40...70 °C
Electrical shock protection class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529


Contractual warranty

Warranty	18 months
----------	-----------

Indicator Bank without Audible Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



Number of illuminated units	b in mm	b in in.
1	108	4.25
2	170	6.69
3	232	9.13
4	294	11.57
5	356	14.02

XVPC6M6W is replaced by:



Illuminated LED units XVUC29

Ø60mm LED unit - steady/flash/rotate, multicolor unit, IP65, 24VAC/DC

Qty 1

Reason for Substitution: End of life | Substitution date: 01 July 2014