

Main

Range of product	OsiSense XU
Series name	General purpose single mode
Electronic sensor type	Photo-electric sensor receiver
Sensor name	XUL
Sensor design	Compact
Detection system	Reflex
Material	Plastic
Type of output signal	Discrete
Supply circuit type	DC
Wiring technique	3-wire
Discrete output type	NPN
Discrete output function	1 NO or 1 NC programmable
Electrical connection	Cable
Cable length	2 m
Emission	Red reflex
[Sn] nominal sensing distance	6 m reflex need reflector XUZC80

Complementary

Enclosure material	ABS
Lens material	PMMA
Maximum sensing distance	9 m with reflector Ø 80 mm
Output type	Solid state
Output function governance	Light or dark programmable
Add on output	Without
Cable composition	4 x 0.34 mm ²
Wire insulation material	PVC
Cable outer diameter	6 mm
Status LED	1 LED for output state
[Us] rated supply voltage	12...24 V DC with reverse polarity protection
Supply voltage limits	10...30 V DC
Switching capacity in mA	<= 100 mA (overload and short-circuit protection)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Switching frequency	<= 250 Hz
Voltage drop	<= 1.5 V (closed state)
Current consumption	<= 35 mA (no-load)
Delay first up	<= 15 ms
Delay response	<= 2 ms
Delay recovery	<= 2 ms
Setting-up	Without sensitivity adjustment
Depth	35 mm
Height	70 mm
Width	18 mm

Environment

Product certifications	CE
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Vibration resistance	7 gn, amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock resistance	20 gn (duration = 11 ms) conforming to IEC 60068-2-27
IP degree of protection	IP671 conforming to NF C 20-010 IP67 conforming to IEC 60529



Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2013 Will be compliant on 3Q2013
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------

XULJ06353R is replaced by the following group of products:

	<p>General purpose XUK1ANANL2 photo-electric sensor - XUK - reflex - Sn 7m - 12..24VDC - cable 2m Qty 1</p>
	<p>General purpose XUZASK003 accessory for sensor - XUK - fixing bracket - metal - for XUL substitution Qty 1</p>

Reason for Substitution: End of life | Substitution date: 01 January 2016

Or XULJ06353R is replaced by:



General purpose XUK0AKSAL2

photo-electric sensor - XUK - multi - Sn 0..30m - 12..24VDC - cable 2m

Qty 1

Reason for Substitution: End of life | Substitution date: 30 September 2005
