



Main

Range of product	Preventa Safety detection
Product or component type	Safety light curtains receiver type 4
Series name	Optimum
Device short name	XUSLB
Product compatibility	XUSLBR5A2120
Output type	1 auxiliary output solid-state PNP 2 safety outputs OSSD solid-state PNP (NO) (short-circuit protection)
Product specific application	For hand protection
Minimum object diameter for detection	30 mm
[Sn] nominal sensing distance	8 m with PDM 0.3...20 m
Height protected	2120 mm
Number of beams	106

Complementary

Detection system	Transmitter-receiver system
Response time	32 ms
[EAA] effective aperture angle	2.5 ° at 3 m
[Us] rated supply voltage	24 V DC (+/- 20 %) against reverse polarity
[Ie] rated operational current	2 A
Current consumption	450 mA no-load 1.8 A with maximum load
Output current limits	625 mA for safety outputs OSSD 100 mA for auxiliary output
Output voltage	24 V
Output circuit type	DC
Monitoring act of of relay MPCE/EDM	50 mA
Local signalling	4 LEDs stop, run, interlock, ECS/B Blanking or FB (Floating Blanking)
Electrical connection	1 female connector M12 8 pins
Marking	CE
Material	Casing : aluminium End caps : 20 % fibre glass impregnated nylon
Fixing mode	End brackets

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	Machinery directive 2006/42/EC ANSI B11:19-1990 EN/IEC 61496-1-2 for type 4 ESPE ROHS directive 2002/95/EC Work equipment directive 2009/104/EC ANSI/RIA R15.06 EN/IEC 61496-1 OSHA 1910-212 EMC 2004/108/EC OSHA 1910-217C EN/IEC 61496-2
Product certifications	UL TÜV CSA
Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-25...75 °C
Relative humidity	0...95 % without condensation
IP degree of protection	IP65
Shock resistance	10 gn for 16 ms conforming to IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm (f = 10...55 Hz) conforming to IEC 61496-1

Contractual warranty

Warranty period	18 months
-----------------	-----------