



Main

Range of product	Preventa Safety detection
Product or component type	Safety light curtains transmitter type 4
Device short name	XUSLP
Product compatibility	XUSLPZ2A0600B
Design	Compact
Product specific application	For body protection
Minimum object diameter for detection	600 mm
[Sn] nominal sensing distance	0.8...20 m depending on configuration 0.8...70 m depending on configuration
Height protected	400 mm
Number of beams	2

Complementary

Detection system	Transmitter-receiver system
Response time	< 16 ms light beam coding C < 20 ms light beam coding B < 24 ms light beam coding A
[EAA] effective aperture angle	2.5 ° at 3 m
Light source	GaAIAs LED, 850 nm
[Us] rated supply voltage	24 V DC (+/- 20 %) against reverse polarity
[Ie] rated operational current	2 A
Current consumption	100 mA
Monitoring act of of relay MPCE/EDM	50 mA
Local signalling	2 LEDs power supply, diagnostic
Electrical connection	Terminal block
Marking	CE
Material	Casing : aluminium End caps : 20 % fibre glass impregnated nylon Front face : acrylic
Fixing mode	End brackets

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	ANSI B11:19-1990 ANSI/RIA R15.06 EN/IEC 61496-1 EN/IEC 61496-1-2 for type 4 ESPE EN/IEC 61496-2 OSHA 1910-212 OSHA 1910-217C ROHS directive 2002/95/EC Machinery directive 2006/42/EC EMC 2004/108/EC Work equipment directive 2009/104/EC
Product certifications	CSA TÜV UL
Ambient air temperature for operation	0...55 °C
Ambient air temperature for storage	-25...75 °C
Relative humidity	0...95 % without condensation
IP degree of protection	IP65 IP67
Shock resistance	10 gn for 16 ms conforming to IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm (f = 10...55 Hz) conforming to IEC 61496-1

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------