

# Product data sheet

Specifications



Illuminated unit for modular tower lights, plastic, blue, Ø70, integral "flash" discharge tube, 5 joule, 120 V AC

XVBC6G6

! Discontinued

! Discontinued on: Oct 20, 2020

## Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Indicator bank
Beacon Or Indicator Bank Unit Type	Illuminated unit
Signalling Type	Flashing
Mounting Diameter	70 mm
Component Name	XVBC
Material	Polycarbonate
Light Source	Integral flash discharge tube, blue
Bulb Type	Flash discharge tube
[Us] Rated Supply Voltage	120 V AC
Flash Energy	5 J

## Complementary

Assembly Style	Customer assembly, up to 5 units
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm <sup>2</sup> with cable end
[UI] Rated Insulation Voltage	250 V conforming to IEC 60947-1
Nominal Voltage Limit	0.85...1.1 Un conforming to IEC 60947-5-1
Current Consumption	< 140 mA AC
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1
Flashing Frequency	1 Hz
Cad Overall Width	70 mm
Cad Overall Height	157 mm
Cad Overall Depth	70 mm
Net Weight	0.28 kg

## Environment

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	EN/IEC 60947-5-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Electrical Shock Protection Class	Class I on support tube conforming to IEC 61140 Class II on base unit conforming to IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. conforming to IEC 60529 IP66 on base unit conforming to IEC 60529
Nema Degree Of Protection	Type 4X conforming to UL (indoor)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	8 cm
Package 1 Length	18.7 cm
Package 1 Weight	273 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards


Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Dimensions Drawings

Indicator Bank with “Flash” Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



- (1) Base unit XVBC07, to be ordered separately
- (2) Illuminated or audible signalling unit XVBC•••, to be ordered separately
- (3) “Flash” unit

Number of illuminated or audible signalling units other than “flash” tube	b in mm	b in in.
1	295	11.61
2	358	14.09
3	421	16.57
4	484	19.06