

# Product data sheet

Specifications



white flush/black flush illuminated  
double-headed pushbutton Ø22  
unmarked

ZB5AW811723

⚠ Discontinued on: Jan 29, 2021

⚠ Discontinued

## Main

Range Of Product	Harmony XB5
Product Or Component Type	Head for illuminated double-headed push-button
Product Compatibility	Integral LED
Device Short Name	ZB5
Bezel Material	Plastic
Mounting Diameter	22 mm
Sale Per Indivisible Quantity	1
Shape Of Signaling Unit Head	Rectangular
Type Of Operator	spring return
Operator Profile	2 flush push-buttons - 1 central pilot light
Operators Description	White unmarked - black unmarked

## Complementary

Cad Overall Width	28 mm
Cad Overall Height	47 mm
Cad Overall Depth	32 mm
Net Weight	0.022 kg
Operator Profile	Black flush, unmarked White flush, unmarked
Mechanical Durability	1000000 cycles

## Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Electrical Shock Protection Class	Class II conforming to IEC 60536
Ip Degree Of Protection	IP40
Nema Degree Of Protection	NEMA 13 NEMA 4X
Resistance To High Pressure Washer	7000000 Pa at 55 °C, distance : 0.1 m
Ik Degree Of Protection	IK05 conforming to IEC 50102

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-1
	EN/IEC 60947-5-4
	EN/IEC 60947-5-1
	JIS C8201-5-1
	CSA C22.2 No 14
	UL 508
	JIS C8201-1
Product Certifications	UL listed
	GL
	CSA
	BV
	DNV
	LROS (Lloyds register of shipping)
Vibration Resistance	5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27
	50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

## Contractual warranty

Warranty	18 months
----------	-----------