



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	M18 plunger head
Product compatibility	XCMD XCKD XCKP XCKT
Associated body	ZCP26 ZCD28 ZCD29M12 ZCD21M12 ZCP21M12 ZCP31 ZCP37 ZCT25P16 ZCD39 ZCP28 ZCD35 ZCT27G11 ZCD26 ZCT21N12 ZCT21G11 ZCP39 ZCD25 ZCP21 ZCT28P16 ZCT28G11 ZCD21 ZCT28N12 ZCD29 ZCP35 ZCT26P16 ZCD31 ZCT21P16 ZCT26N12 ZCD27 ZCP29

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCT25G11  
ZCT27N12  
ZCT27P16  
ZCP25  
ZCD37  
ZCP27  
ZCT25N12  
ZCP29M12  
ZCT26G11

Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach 1 direction

### Complementary

Positive opening	With
------------------	------

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------